



Part Number: 32935

Description: Journeyman's Tool Set 30-Piece

The Wiha Journeyman's tool set has the tools electricians and technicians need to get the job done plus the peace of mind of using individually tested, 1,000 Volt Rated, Insulated VDE screwdrivers, pliers, and nut drivers. The set contains common tools for electricians like "tweaker" sized precision drivers, a level, tape measure, wire strippers, adjustable pliers, magnetic nut setters, a "demo driver" heavy duty screwdriver, voltage detector, and a hammer for everyday work. The Wiha Journeyman's tool set will have the tools you need stored in a rugged nylon bag.



Details

Wiha Insulated Tools

- 1000 Volt Rated, 10,000 Volt Tested
- Comply with one or more of the following standards: VDE, ASTM, IEC, CSA, OSHA, EN/IEC, NFPA.
- All Tools Individually tested for maximum safety performance

Insulated PicoFinish Precision Screwdrivers

- Slotted 2.5mm x 6.2-Inch
- Slotted 3.0mm x 6.2-Inch
- Slotted 3.5mm x 6.2-Inch
- Phillips #0 x 6.2-Inch
- Phillips #1 x 6.2-Inch

Insulated SoftFinish® Screwdrivers

- Slotted 4.0mm x 8.3-Inch
- Slotted 4.5mm x 9.3-Inch
- Slotted 6.5mm x 10.6-Inch
- Phillips #1 x 7.5-Inch
- Phillips #2 8.6-Inch
- Square #2 10.5-Inch

Extra Heavy Duty Screwdrivers

- Slotted 8.0mm x 10.6-Inch with steel striking cap and hex bolster

Insulated Nut Drivers

- 1/4" x 9.6-Inch
- 5/16" x 9.6-Inch
- 3/8" x 9.6-Inch

Insulated Pliers

- 8-Inch Insulated. Industrial Long Nose Pliers
- 9.5-Inch. New England Style Lineman's High Leverage Pliers
- 8-Inch Insulated Heavy Duty Diagonal Cutters
- 8-Inch Insulated Industrial Serrated Edge Cable Cutters
- 10-Inch Insulated Water Pump Pliers

Soft Grip Pliers

- 10-Inch Soft grip auto pliers
- 7.25-Inch 10-20 AWG Wire Strippers

Magnetic Nut Setters

- 1/4" x 4-Inch
- 5/16" x 4-Inch
- 3/8 x 4-Inch

Everyday Tools

- Category III Voltage Detector 110V
- 25 Ft. Wiha Measuring Tape
- 20 oz. Cushion Grip Claw Hammer
- 9" Magnetic Torpedo Level

Additional Info

SKU	32935
Weight (lbs)	14.8800
California Residents	Click for Proposition 65 warning
Head Type	slotted, phillips, square, inch nut setters, nut driver inch
Pieces In Set	30
Grip Type	Insulated
Handle Grip Types	MicroFinish®, Insulated SoftFinish®, Precision PicoFinish, Precision
Phillips Sizes	#0 #1 #2
Slotted Sizes	2.5mm ~3/32" 3.0mm~1/8" 3.5mm~9/64" 4.0mm~5/32" 4.5mm~11/64" 6.5mm~1/4" 8.0mm~5/16"
Square Sizes	#1, #2
Inch Nut Driver Sizes	1/4" 5/16" 3/8"
UPC	084705329352