

4-Slot USB-C SD Card Reader - USB 3.1 (10Gbps) - SD 4.0, UHS-II

Product ID: 4SD4FCRU31C



This USB-C™ SD™ card reader lets you access four SD cards simultaneously.

You can:

- Download and edit photos and videos
- Back up documents and critical data from multiple users
- Deploy system updates in batches
- Distribute content to multiple employees

The card reader transfers files between your USB-C, Thunderbolt 3 or USB-A laptop or desktop computer and the reader.

Ultra-Fast Read/Write Access

The reader features SD 4.0 and UHS-II support. It reads and writes to and from the cards at speeds of up to 312MB/s. The reader also supports USB 3.1 connection speeds of up to 10Gbps to ensure maximum transfer rates between the computer and the reader, while simultaneously accessing all four cards.

The card reader is also backward compatible with earlier versions of USB (3.0, 2.0 and 1.1).

Multi SD Card Reader Supports All SD Card Types

The card reader supports all SD cards: SD (Secure Digital), SDHC™ (Secure Digital High Capacity) and SDXC™ (Secure Digital Extended Capacity). It also supports UHS cards, and is backward compatible with older SD card versions.

The card reader will also support the following card types when connected through an adapter:

- microSD™
- miniSD™
- MMCmobile™
- RS-MMC™
- MMCplus™

Compact Design

The small footprint design fits in nicely with your workstation. Place the card reader on your desk without taking up too much space.

4SD4FCRU31C comes with a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Access four SD cards simultaneously

Features

- Save time and access four SD cards simultaneously with this multi SD card reader
- Ensure maximum transfer rates while accessing all four cards with connection speeds of up to 10Gbps
- Perform fast read and/or writes with support for SD 4.0, UHS-II and bus speeds up to 312MB/s
- Access more cards, the card reader supports all SD types: SD, SDHC, and SDXC
- Easily integrate this USB-C SD card reader into your workstation with its compact design

Hardware	Warranty	2 Years
	Chipset ID	Genesys Logic - GL3590 Genesys Logic - GL3227
	Interface	USB 3.1 Gen 2
Performance	Memory Media Type	SD/MMC (Secure Digital/Multimedia Card) SDHC (Secure Digital High Capacity) SDXC (Secure Digital eXtended Capacity)
	Type and Rate	USB 3.1 Gen 2 - 10 Gbit/s UHS-II (SD 4.0; 312MB/s)
Connector(s)	Drive Connectors	4 - SD / MMC Slot Female
	External Ports	4 - SD / MMC Slot Female
	Host Connectors	1 - USB Type-C (24 pin) USB 3.1 (10Gbps) Female
Software	OS Compatibility	OS independent; No software or drivers required
Indicators	LED Indicators	4 - Activity
Power	Center Tip Polarity	Positive
	Input Current	1 A
	Input Voltage	110V-240V AC
	Output Current	2.4 A
	Output Voltage	5 DC
	Plug Type	B
	Power Source	AC Adapter Included
Environmental	Humidity	0~60% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Physical Characteristics	Form Factor	Compact
	Product Height	0.7 in [17 mm]
	Product Length	7 in [177 mm]
	Product Weight	11.8 oz [335 g]
	Product Width	2.8 in [70 mm]
Packaging Information	Shipping (Package) Weight	11.8 oz [335 g]
What's in the Box	Included in Package	1 - SD card reader

- 1 - 3 ft. [0.9 m] USB-C to USB-C cable
- 1 - 3 ft. [0.9 m] USB-A to USB-C cable
- 1 - universal power adapter (NA/JP, EU, UK, ANZ)
- 1 - quick-start guide

Product appearance and specifications are subject to change without notice.