

PS12_LCAS_0000_SM09E_S0

Description

12 pigtail set, LC-HQ BTW, APC, fiber 0.9mm_XX.X_fiber colour EN / IEC, SM G.652.D



| Features | Features |
|---|----------|
| - High mechanical stability | |
| - Colour coded boot for good visibility also in mated condition | |

Technical Data

General Data

| Description | Values |
|---------------------------|----------------|
| Operation temperature | 85 up to -40°C |
| UL Rating | UL 94 V-0 |
| RoHS compliant 2001/65/EU | Yes |
| REACH compliant | Yes |


Connector left

| Description | Values |
|---------------------------------|----------------------------|
| Connector typ | LC pigtail |
| Polish | APC |
| Color Housing | Black |
| Color Boot | Green |
| Design connector acc. To | IEC 61754-20, TIA 604-10-A |
| Performance class H+S | 0 |
| Insertion loss 97% dB / mean dB | 0.25 / 0.12 |
| Return Loss | >65dB |
| Durability | 1000 |

Cable

| Description | Values |
|-------------|----------------------------|
| Cable typ | Semi-tight Tube |
| Fiber count | 1 |
| Fiber | 1 x 0.9 mm |
| Fiber typ | E9/125-SM standard G.652.D |

Technical Drawing



Ordering information

| Meter (m) | Item number | Description |
|-----------|-------------|-------------|
|-----------|-------------|-------------|

