

# LAN/Length Cable Tester

## TCT-2690PRO



### Specifications:

Display	144 x 64 Dots FSTN LCM
Connector Type	F/RJ45
Cable Types	Shielded or unshielded CAT-7, CAT-6, CAT-5E, CAT-5, CAT-4, CAT-3 and Coax cable
Error Status	Open circuit, short circuit, jumper wire, reverse, connection or cross-talk interference and split pairs
Measurements	Measures cable length via TDR Checks and verifies wire map Generates four different tracing tones to identify users
Cable Length	1-350 meters (3-1200 feet)
Accuracy	± 5 %
Minimum cable length	1 meter
Power source	9V alkaline battery
Operating Temperature	0° to 50° C (32° to 122° F)
Storage Temperature	-10° to 60° C (14° to 140° F)
Humidity	10 % to 90 % non-condensing
Accessories	Tool Bag x 1 pcs , F to BNC Adapter x 2 pcs , RJ45 to USB Adapter x 2 pcs , RJ45 to RJ11 Adapter x 2 pcs , ID1 ~ ID8 x 1 set