

SMART MUSIC LED CEILING LIGHT

SKU Code: SHA5255
EAN Code: 7103356611517



Features

- Download our free App, connect with your Bluetooth and pair within 2 minutes.
- Change Colors, dim lights, play music from your smart phone.
- Easy Installation, with magnetic holder.

Specification

Input Voltage	85-265V AC / 50-60Hz
Power	24W
LED	RGB: 24pcs 5050, warm white: 48pcs 5730, cool white: 48pcs 5730
Color	RGB multi color + white color
Color Temperature	3000K-6500K dimmable (PWM)
CRI	Warm white>85, cool white>75
View Angle	270°
Audio Power	10W, 4Ω, THD+ η =10%, 1KHz
Frequency Response	40Hz-18KHz, Non uniformity: 3dB
Audio Distortion (HTD+ η)	<1%, P=1W, 1KHz
Signal to Noise Ratio (SNR)	>80dB, P=1W, A-weight
Volume Control	APP, connect by Bluetooth (4.0)
Bluetooth Distance	>10m, Straight line distance and no obstacles
Dimension	D405×H110mm(big)



Download
Our App



iLink

