



THE WORLD LEADER IN LADDERS™

Multi-Purpose Ladder - Telescopic


MT-SERIES

The most versatile ladder you can own



TELESCOPIC DESIGN

For quick adjustment to various heights for different projects.



DOUBLE RIVETED STEPS

For long lasting durability



EASY TO OPERATE HINGE LOCKS

Transform the ladder between modes



STEPLADDER



EXTENSION LADDER



STAIRWELL LADDER



2 SCAFFOLD BASES

Plank and tie-downs not included

Visit us online to see our range of products
www.wernerladder.co.uk



THE WORLD LEADER IN LADDERS™

MT-SERIES

Multi-Purpose Ladder - Telescopic



Combines a stepladder, extension ladder, stairwell ladder and scaffold base all in one product



Compact folded dimensions, easy to use, transport and store




Self Supporting Scaffold Base
*plank and tie downs not included

150kg
LOAD CAPACITY
(Load includes user, tools, materials, etc.)



Adjustable, telescopic sections and simple 'Click-Lock' hinge system



Double riveted steps for long lasting durability



Slip-resistant feet and splayed base for extra stability

Model 75054

SPECIFICATIONS

| Code | Section x Rungs | Safety | Max. Load | Closed Length | Ext. Ladder Length | Safe Working Height* in extension ladder mode | Product Weight |
|-------|-----------------|-------------------|-----------|---------------|--------------------|---|----------------|
| 75053 | 4 x 3 | Conforms to EN131 | 150kg | 1.00m (3'3") | 2.88m (9'5") | 3.63m (11'11") | 11.75kg |
| 75054 | 4 x 4 | Conforms to EN131 | 150kg | 1.30m (4'3") | 3.98m (13'1") | 4.97m (16'4") | 14.2kg |
| 75055 | 4 x 5 | ANSI Type 1A | 136kg | 1.75m (5'9") | 5.79m (19'0") | 6.71m (22'0") | 19.8kg |
| 75056 | 4 x 6 | ANSI Type 1A | 136kg | 2.05m (6'9") | 7.01m (23') | 7.87m (25'10") | 27.3kg |

*Based on 1.75m (5'9") as the average reach height of a person.