

Accessories - PTCM-MP-PI 0,14-0,5 - 1013990

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, type of contact: Male connector, connection method: Crimp connection, contact surface: Tin



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
GTIN	 4 055626 494272
GTIN	4055626494272
Weight per Piece (excluding packing)	0.400 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

General

Range of articles	PTCM-MP-PI
-------------------	------------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.1	27260700
eCl@ss 6.0	27260700

Accessories - PTCM-MP-PI 0,14-0,5 - 1013990

Classifications

eCl@ss

eCl@ss 7.0	27440309
eCl@ss 8.0	27440204
eCl@ss 9.0	27440204

ETIM

ETIM 5.0	EC000796
ETIM 6.0	EC002638

Accessories

Accessories

Crimping tool

Crimping pliers - CRIMPFOX-P CC 0.75 L - 1064998



Crimping pliers, for COMBICON crimp connectors with cross section: 0.14 ... 0.75 mm². Unlockable pressure lock, precise parallel crimping, front entry, B crimp, incl. 2 positioning aids

Additional products

Printed-circuit board connector - PTCM 0,5/ 2-PI-2,5 WH - 1015242



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 2, pitch: 2.5 mm, connection method: Crimp connection, color: white

Printed-circuit board connector - PTCM 0,5/ 3-PI-2,5 WH - 1015243



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 3, pitch: 2.5 mm, connection method: Crimp connection, color: white

Accessories - PTCM-MP-PI 0,14-0,5 - 1013990

Accessories

Printed-circuit board connector - PTCM 0,5/ 4-PI-2,5 WH - 1015244



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 4, pitch: 2.5 mm, connection method: Crimp connection, color: white

Printed-circuit board connector - PTCM 0,5/ 5-PI-2,5 WH - 1015245



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 5, pitch: 2.5 mm, connection method: Crimp connection, color: white

Printed-circuit board connector - PTCM 0,5/ 6-PI-2,5 WH - 1015246



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 6, pitch: 2.5 mm, connection method: Crimp connection, color: white

Printed-circuit board connector - PTCM 0,5/ 7-PI-2,5 WH - 1015247



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 7, pitch: 2.5 mm, connection method: Crimp connection, color: white

Printed-circuit board connector - PTCM 0,5/ 8-PI-2,5 WH - 1015248



PCB connector, nominal current: 6 A, rated voltage (III/2): 160 V, number of positions: 8, pitch: 2.5 mm, connection method: Crimp connection, color: white
