

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192160003](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Multi-Lock Connector for 14-16 AWG Wire

**Documents:**

[3D Model](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#)

**Agency Certification**

UL E32244

**General**

Product Family Splices  
 Series [19216](#)  
 Comments 13.97 x 9.53mm when closed, 13.97 x 9.53mm when closed  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Splices](#)  
 Product Name Multi-Lock  
 UPC 800753056138

**Physical**

Barrel Type Closed  
 Color - Resin Blue  
 Flammability 94V-0  
 Insulation Polypropylene  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 1.267/g  
 Packaging Type Bag  
 Temperature Range - Operating 105°C  
 Wire Insulation Diameter 3.30mm & 4.32mm  
 Wire Size AWG 14, 16  
 Wire Size mm<sup>2</sup> N/A

**Electrical**

Voltage - Maximum 600V

**Solder Process Data**


Lead-free Process Capability N/A

**Material Info**

Engineering Number ML-1614

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19216-003



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/88/2018 (15  
 January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19216 Series](#)