

PowerWalker Basic VI 600-2200 STL Series

- Human Interface Device (HID) compatible USB connection (no additional drivers needed)
- Multi-purpose button (single-click, double-click or hold to control different functions)
- Auto dimming screen (UPS is woken up with single button click)
- Equipped with Boost and Buck AVR to stabilize output voltage
- Reduced environmental impact: no CD, no USB cable in the box
- Available with outlets type E, F and G

2018 PREMIERE



The PowerWalker Basic VI 600/800/1000/1200/1500/2200 STL series is designed to answer the essential market needs. This line interactive UPS will protect your load from power failures and voltage disturbances, while remaining affordable and compact. It is equipped with a USB port with HID support allowing easy and immediate communication with any O/S.



Additionally this series offers an advanced auto-dimming LCD panel with a smart multi-functional button (a single click will illuminate the LCD panel, a double click will mute the alarm and a long-press will control the output).



HID Support

The managing software PowerWalker PowerMaster is available for download from our website:

www.powermaster.powerwalker.com.

MODEL	VI 600 STL	VI 800 STL	VI 1000 STL	VI 1200 STL	VI 1500 STL	VI 2200 STL
Item Number (Type F outlet)	10121072	10121073	10121074	10121075	10121076	10121077
Item Number (Type E outlet)	10121078	10121079	10121080	10121081	10121082	10121083
Item Number (Type G outlet)	10121084	10121085	10121086	10121087	10121088	10121089
POWER						
Power (kVA)	600VA	800VA	1000VA	1200VA	1500VA	2200VA
Power (kW)	360W	480W	600W	720W	900W	1320W
INPUT						
Voltage	162-290 VAC					
Plug	Standard: Type F or British Type G					
Frequency Range	Auto-sensing at 50Hz 60Hz					
OUTPUT						
Voltage	230 VAC $\pm 10\%$					
Frequency Range	50Hz or 60Hz $\pm 1\%$					
Waveform	Simulated Sine Wave					
Switching Time	Typical 4ms					
Outlets	2 x Type F or 2x Type E (French) or 2x Type G (British)			4 x Type F or 4x Type E (French) or 4x Type G (British)		
EFFICIENCY						
AC Mode	95,3%	96,7%	96,8%	95,8%	95,8%	95,7%
Fan	No			Yes		
COMMUNICATION						
Port	USB Port with HID support (cable not provided)					
Software	PowerWalker PowerMaster available on website					
BATTERY						
Amount	1x7Ah/12V	1x7.2Ah/12V	1x9Ah/12V	2x7Ah/12V	2x7.2Ah/12V	2x9Ah/12V
Charging Time	8h to 90%					
Half-Load backup time	5min	5min	5.5min	7.5min	7.5min	3.9min



PowerWalker Basic VI 600-1000 STL with outlets: Type F, Type E, Type G



PowerWalker Basic VI 1200-2200 STL with outlets: Type F, Type E, Type G

04/04/2018