

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0524652071](#)  
**Status:** **Active**  
**Overview:** SlimStack™ 0.35mm pitch Board-to-Board Connectors  
**Description:** SlimStack Board-to-Board Connector, 0.80mm Pitch, Floating Series, Rigid Type Receptacle, 4.50 to 7.00mm Mated Height, 20 Circuits, without Boss

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification SPK-52465-002-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-52465-010-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Product Specification PS-52465-014-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Product Specification PS-52465-015-001 (PDF)</a>	

**General**


Product Family	PCB Receptacles
Series	<a href="#">52465</a>
Application	Board-to-Board, Signal
Datasheet Order No	987651-8814, 987651-8815_ZH, 987651-8817_DE, 987651-8818_JA, 987651-8819_KO, 987651-8820_ES
Overview	<a href="#">SlimStack™ 0.35mm pitch Board-to-Board Connectors</a>
Product Guide Order No	987651-8281
Product Literature Order No	987652-0196, Reference Guide#
Product Name	SlimStack
Series Name	0.80 Floating
UPC	822348142972

**Physical**

Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Natural
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	4.50mm, 5.65mm, 6.00mm, 7.00mm
Mated Width	4.70mm, 5.10mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	207.400/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.80mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to PCB	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[52465 Series](#)

**Mates With**

[53364](#) , [53353](#) , [53307](#) , [53309](#)

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification

Product Specification

Sales Drawing

SPK-52465-002-001

PS-52465-010-001, PS-52465-014-001,

PS-52465-015-001

SD-52465-028, SD-52465-029

This document was generated on 04/02/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**