

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5022311500](#)
Status: **Active**
Overview: FFC-FPC (SMT)
Description: 0.50mm Pitch Easy-On FFC/FPC Connector, For LVDS, 6.05mm Height, Vertical, Surface Mount, ZIF, 15 Circuits

Documents:

[3D Model](#) [Product Specification PS-502231-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family FFC/FPC Connectors
 Series [502231](#)
 Overview [FFC-FPC \(SMT\)](#)
 Product Name Easy-On
 UPC 822350669009

Physical

Actuator Type Flip
 Circuits (Loaded) 15
 Color - Resin Brown, Natural
 Contact Position N/A
 Durability (mating cycles max) 20
 Mated Height 6.05mm
 Material - Metal Phosphor Bronze
 Material - Plating Mating Gold, Tin
 Material - Plating Termination Gold, Tin
 Net Weight 339.180/mg
 Number of Rows 1
 Orientation Vertical
 PCB Locator No
 PCB Mounting Surface Mount
 PCB Retention Yes
 Packaging Type Embossed Tape on Reel
 Pitch - Mating Interface 0.50mm
 Pitch - Termination Interface 0.50mm
 Polarized to PCB Yes
 Stackable No
 Temperature Range - Operating -25° to +85°C
 Wire/Cable Type FFC only


Electrical

Current - Maximum per Contact 0.4A
 Voltage - Maximum 50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Product Specification PS-502231-001-001
 Sales Drawing SD-502231-001, SD-502231-002



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[502231 Series](#)

Use With

LVDS Cable [15021](#)