



Part Number: J5000-BWSSFID

Description: BradyJet J5000 Colour Label Printer with Brady Workstation Safety and Facility ID Software Suite Kit

Product Highlights

Maximum Label/Tape Width: 8.25 in

Color Printing Capability: Full Color

Maximum Labels per Day: 5000

Printer and Label Applications: General Identification, Hazardous Materials, Lean / 5S, Pipe Marker, Safety




Overview

Get an easy start on your safety and facility identification projects with the BBP®85 printer and Brady Workstation Safety and Facility Identification Software Suite.

- Create photo-quality signs and labels in a single pass with The BradyJet™ J5000 printer. This on-demand inkjet solution reduces your label supplies inventory and material waste.
- Easily create custom signs, labels and pipemarkers with the Safety and Facility Identification Suite to keep your facility safe and compliant
- More than 16 million color possibilities, ideal for labels with photos, graphics, illustrations, text, linear and 2D bar codes and more
- 4800 dpi print resolution for high-resolution clarity and fine detail
- Setup is stress free – Contact our Brady Technical Support Team and we will schedule a free phone setup appointment

Specifications

Automatic Label Set Up	Yes
Barcode Capability	Barcode Capable
Country of Origin	MY - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
Calibration Required?	No
California Prop 65	 WARNING: Cancer and Reproductive Harm - www.p65warnings.ca.gov
Color Printing Capability	Full Color
Custom Media Parts Available	No
Dimensions	10.2 in H x 19.5 in W x 20.5 in D
Display Size	1.25" x 1.25"
UOM	Kit
Estimated Media Changeover Time	Change labels in less than 20 s, change ink cartridge in less than 10 s
Maximum Printed Label Length	24 in
Maximum Label/Tape Width	8.25 in
Maximum Liner Width	8.25 in
Maximum Print Speed	6 in/s
Maximum Print Width	8.0 in
Minimum Label Length	0.5 in
Number of Symbols	See Brady Workstation Software
Special Characters Quantity	See Brady® Workstation
Power Supply Voltage	100 to 240 V @ 50 to 60 Hz

Print Resolution	4800 dpi
Product Number	149577
UPC	754473607470
Trade Name	BradyJet™
UNSPSC	45101519
Warranty	1 Year
Weight	45 lb
Applications	General & Industrial ID, OHS & Chemical Labels, Lean/5S, Pipe & Valve Marking, Visual Workplace Labeling, Warehouse Marking
Barcode Symbologies - Linear	More Through Brady Workstation
Barcode Symbologies - 2D	More Through Brady Workstation
Label Material Types	General Purpose Vinyl, Polyester
Connectivity Options	Ethernet, USB, Wi-Fi
Continuous & Die-Cut Materials Supported	Continuous Tapes & Die-Cut Labels
Cutter Type	Auto Cutter
Display Type	Color LCD
Includes	25000 Printer, Brady Workstation SFID Software Suite
Languages Available	Chinese (Simplified), Chinese (Traditional), Dutch, English (US), French (France), German, Italian, Japanese, Korean, Spanish (Spain)
Maximum Labels per Day	5000
Media Sensor Type	See-Through
Mode of Operation	Peripheral Mode
Plug Type	US
Printer and Label Applications	General Identification, Hazardous Materials, Lean / 5S, Pipe Marker, Safety
Print Technology	Ink Jet
User Interface Type	PC