



PicoFinish Precision Screwdrivers Phone Repair Set



SKU: 26198

T5 x 134mm OAL
T6 x 140mm OAL

Details

PicoFinish Precision Screwdrivers

Smooth Rotating cap with tip size and icon for easy identification
Comfortable grip precision screwdriver for precision screws

Pentalobe

PL1 x 134mm OAL

Triwing or Y-Type

Y000 x 134mm OAL

Precision Sizes Included

Phillips

#000 x 134mm OAL
#00 x 134mm OAL
#0 x 150mm OAL

Torx

T3 x 134mm OAL
T4 x 134mm OAL

Additional Info

SKU 26198
Weight (lbs) 0.5900
Head Type slotted, phillips, torx, pentalobe, tri point

Handle Grip Types Precision PicoFinish

Phillips #000
#00

Sizes #0

Slotted 1.8mm~1/16"
Sizes

Torx T3
T4
T5
T6
Sizes

5 Point PL1

/

Pentalobe
obe
Sizes

Size Tri-Point 000
UPC 084705261980

Slotted

1.8mmx0.3mm ~ 1/16" x 134mm OAL

ESD Safe Tweezers

Special alloyed, non-rusting, stainless Steel
Coated by ESD-Safe dissipative material
Anti magnetic and acid resistant
