



DR TAPE

For telephone cable splicing and insulation of exchange station and outside distributing wire

Technical Data Sheet

October 2017

Description and Features	DR is a two-layered tape with a white unvulcanized rubber tacky face (1/2 of total thickness) permanently bonded to a layer of black vulcanized rubber, which provides the required mechanical strength. The white tacky side is covered with a removable Holland Cloth separator. <ul style="list-style-type: none">▪ Controlled removal of separator▪ Forms air-tight, water-proof, gas-tight seal when uncured layer is bonded to itself.			
Materials	Backing Rubber	Adhesive None	Color Black	Standard Size Width x Length 51 mm x 4,6 m (2 in. x 15 ft.) Other sizes available upon request
Technical Properties	Characteristic	Typical Value	Test Method	
	Thickness (mm)	1,20	ASTM D 4325	
	Adhesion (turns)	0,5	AT 6863	
	Permanent Set Max (mm)	38	AT 6863	
	Tackiness	No unwind	AT 6863	
	Elongation (%)	525	ASTM D 412	
	Tensile Strength (MPa)	5,0	ASTM D 412	
	Heat Stability @ 100 °C	Excellent	AT 6863	
	Weatherometer, 18 hours	No effect	AT 6863	
	Dielectric Strength (kV/mm)	16,0	ASTM D 149	
Recommended Uses	For telephone cable splicing and insulation of exchange station and outside distributing wire splices and connections.			
Storage	In original packaging, placed in horizontal position under cover and temperature between 5°C and 20 °C.			
Shelf Life	12 months from date of manufacture.			

Information provided is for reference only. Data in table represent average test results and are not to be used for specification purposes. The product user should make his/her own tests to determine the product's suitability for the intended use

LIMITED WARRANTY: Plymouth warrants that its Product will substantially conform to that products written specifications for a period of one (1) year from the date of shipment, (Unless provided otherwise). Plymouth makes no warranty to the distributor, its customers, or the product's end user for the products merchantability and/or suitability for his/its intended use or purpose, and buyer shall assume all risks associated therewith. Provided that the product is proved to be defective within the terms described above, and provided buyer shall have first complied with all return policies of Plymouth, PLYMOUTH'S SOLE OBLIGATION AND BUYER'S EXCLUSIVE REMEDY UNDER THIS PRODUCT WARRANTY SHALL BE TO REPLACE SUCH QUANTITY OF THE PRODUCT AS IS PROVED TO BE DEFECTIVE WITHIN THE TIME PERIOD SPECIFIED ABOVE. EXCEPT AS EXPRESSLY SET FORTH HEREIN, PLYMOUTH MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED. In no event shall Plymouth be liable for collateral, consequential, indirect or incidental damages arising out of, or connected in any way with the supply of products. (Rev. 1/2017-2019)