

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1727186121](#)
Status: **Active**
Overview: Mini-Fit Jr. Power Connectors
Description: Mini-Fit TPA2 Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Reel

Documents:

Drawing (PDF)	Packaging Specification PK-172718-0001-000 (PDF)
Product Specification PS-172718-0000-001 (PDF)	Test Summary 1727180001-TS-000 (PDF)
Application Specification AS-172718-0000-001 (PDF)	Test Summary 1727180002-TS-000 (PDF)
Packaging Specification PK-172718-0000-000 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Terminals
Series	172718
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	See product specification for current derating information. See Mini-Fit TPA2 housing series for 3D models., See product specification for current derating information. See Mini-Fit TPA2 housing series for 3D models.
Crimp Quality Equipment Overview	Yes
Packaging Alternative	Mini-Fit Jr. Power Connectors 1727186122 (Bag)
Product Name	Mini-Fit TPA2
UPC	889056179416

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.210/g
Packaging Type	Reel
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65-2.38mm
Wire Size AWG	22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	11.5A
Voltage - Maximum	600V AC/DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-172718-0000-001
Application Tooling Documents	ATS-2002180200, ATS-2002181200, ATS-639037000-001
Packaging Specification	PK-172718-0000-000, PK-172718-0001-000
Product Specification	PS-172718-0000-001
Sales Drawing	SD-172718-0000-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

172718 Series

Use With

Mini-Fit TPA2 Receptacle Housings [172708](#), [200453](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 22 AWG, Large and Small Insulation Grips	2002180200
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 24 AWG,	2002181200

Large and Small
Insulation Grips
Extraction Tool for [638246210](#)
Mini-Fit TPA2 Crimp
Terminal, 16-24
AWG
FineAdjust Applicator [639037000](#)
for Mini-Fit TPA2
Crimp Terminals,
0.22mm², 0.25mm²,
0.35 mm² and 22-24
AWG wires

This document was generated on 04/16/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION