

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0194300004**
Status: **Active**
Overview: Splices
Description: See and Splice 5 Circuit Push-in Wire Connector for 12-22 AWG Wire

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Splices
 Series 19430
 Comments Gray Insert|1000V max. for lighting/sign fixtures, Gray Insert|1000V max. for lighting/sign fixtures
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview Splices
 Product Name See and Splice
 UPC 822348218912

Physical

Barrel Type Closed
 Color - Resin Gray
 Flammability 94V-2
 Insulation None
 Material - Metal Brass
 Material - Plating Mating N/A
 Net Weight 3.557/g
 Packaging Type Bag
 Temperature Range - Operating -30° to +105°C
 Wire Insulation Diameter 3.30mm is the nominal O.D.
 Wire Size AWG 12, 14, 16, 18, 20, 22

Electrical


Voltage - Maximum 600V

Material Info

Engineering Number PC5-GRAY

Reference - Drawing Numbers

Sales Drawing SD-19430-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19430 Series