

Omega Supreme Plus HEPA Cleanroom Vacuum

by **Atrix**™



VACOMEGASECRH

PRODUCT HIGHLIGHTS

WARRANTY

3 Year Limited

CLASS 100,000, ISO 8 CLEANROOM VACUUM

With HEPA Premotor and HEPA Postmotor Filtration

POWERFUL

1,000 Hour Rated Ametek Advantek II Motor

QUIET

69 Decibels

SAFE

DUAL HEPA Filtration along with ESD Safety draining damaging static voltages to ground and built-in electronic line filter to minimize EMI/RFI noise emissions

APPLICATIONS

Class 100,000, ISO 8 Cleanrooms, Clean areas, pharmaceutical, medical, electronic



Ultrafine Vacuums Built to Last. Quality Assured.

www.atrinx.com | sales@atrinx.com | 1-800-222-6154 | Burnsville, MN, USA

Omega Supreme Plus HEPA Cleanroom Vac

by **Atrix**™

SPECIFICATIONS

VACOMEGASECRH

DIMENSIONS

Length: 20" (508 mm)
Width: 6.25" (159 mm)
Height: 9.25" (235 mm)

WEIGHT 12.3 lbs. (5.58 kg)

HOSE DIAMETER

Inside - 1.00" (25.4 mm)
Outside - 1.25" (31.75 mm)

POWER

120, 628W

CFM

99 CFM

FILTRATION

PREMOTOR

HEPA

99.97% Efficient at .3 Micron
1 Gallon Dry
56 Pleat, 3 Layer
One Cellulose Layer
Two Glass L-ayers

POSTMOTOR

HEPA

99.97% Efficient at .3 Micron
4.5"x4"
40 Pleat, 3 Layer
One Cellulose Layer
Two Glass Layers

GENERAL INFORMATION

PACKAGING

Dimensions: L W H
Inches: 20.25 7.75 10.75
mm: 514 197 273
Weight: 13.55 lbs.
6.15 kg

HS Code

8508.11.0000

UPC

8 38067 00110 0

INCLUDED CONTENTS

- A - Omega Supreme Plus HEPA Cleanroom Vac by Atrix
- B - 31651 - 120V Detachable Power Cord
- C - 31657 - ESD Safe Flexible Gooseneck Tool
- D - 31671 - ESD Safe 10' Stretch Hose
- E - OF612HE - HEPA Filter Cartridge
- F - ATIEF - HEPA Filter (postmotor)
- G - 410017 - Filter Plug
- H - AVPA011 - NON-ESD Utility Nozzle
- I - AVPA016 - Adjustable Shoulder Strap



OPTIONAL ACCESSORIES

Omega ULPA Filter Cartridge OF712UL



Omega HEPA Filter Cartridge with Static Dissipative Body - OF912HE



HEPA CERTIFIED Omega Series Filter Cartridge - OF612HE-IC

