

27UL650

27" Class 4K UHD IPS LED Monitor with VESA DisplayHDR 400

EAN CODE: 8806098424450

27"

KEY FEATURES

- 27" UHD (3840 x 2160) IPS Display
- VESA DisplayHDR 400
- sRGB 99% Colour Gamut
- 3-Side Virtually Borderless Display
- Height / Pilot / Tilt Adjustable Stand
- Radeon FreeSync™ Technology



For more information
www.lg.com/uk/monitors

PRODUCT FEATURES

DISPLAY	
Size(Inch / cm)	27"
Resolution	3840 x 2160
Panel Type	IPS
Aspect Ratio	16:9
Pixel Pitch	0.1554 x 0.1554 mm
Brightness	280cd/m ² (Min.) 350cd/m ² (Typ.)
Color Gamut (Typ.)	sRGB 99% (CIE1931)
Color Depth (Number of Colors)	1.07B
Contrast Ratio	700:1 (Min.) 1000:1 (Typ.)
Response Time	5ms (GtG at Faster)
Viewing Angle (CR≥10)	178° (R/L), 178° (U/D)
Surface Treatment	Anti-Glare 3H

SPEAKER	
Type	NO
Audio output (watt)	N/A
Others	NO

POWER	
Type	External Power(Adapter)
AC Input	100-240Vac, 50/60Hz
Power Consumption (Typ.)	36W
Power Consumption (Max.)	43W
Power Consumption (Energy Star)	22W
Power Consumption (Sleep Mode)	Less than 0.5W
Power Consumption (DC Off)	Less than 0.3W

CONNECTIVITY	
D-Sub	NO
D-Sub (Max. Resolution at Hz)	N/A
DVI	NO
DVI (Max Resolution at Hz)	N/A
HDMI	YES(2ea)
HDMI (Max. Resolution at Hz)	3840 x 2160 at 60Hz
DisplayPort	YES (1ea)
DP Version	1.4
DP (Max. Resolution at Hz)	3840 x 2160 at 60Hz
Mini DisplayPort	NO
mDP (Max. Resolution at Hz)	N/A
Thunderbolt	NO
Thunderbolt (USB-C Compatibility)	NO
Thunderbolt (Max. Resolution at Hz)	N/A
Thunderbolt (Data Transmission)	NO
Thunderbolt (Power Delivery)	N/A
USB-C	NO
USB-C (Max. Resolution at Hz)	N/A
USB-C (DP Alternate Mode)	NO
USB-C (Data Transmission)	NO
USB-C (Power Delivery)	N/A
Daisy Chain	NO
USB Upstream Port	NO
USB Downstream Port	NO
Audio In	NO
Mic In	NO
Headphone Out	YES
Line Out	NO

27UL650

27" Class 4K UHD IPS LED Monitor with VESA DisplayHDR 400

EAN CODE: 8806098424450

27"

KEY FEATURES

- 27" UHD (3840 x 2160) IPS Display
- VESA DisplayHDR 400
- sRGB 99% Colour Gamut
- 3-Side Virtually Borderless Display
- Height / Pivot / Tilt Adjustable Stand
- Radeon FreeSync™ Technology

For more information
www.lg.com/uk/monitors

PRODUCT FEATURES

FEATURES

HDR 10	YES
VESA DisplayHDR™	DisplayHDR™ 400
HDR Effect	YES
Nano IPS™ Technology	NO
Wide Color Gamut	NO
Color Calibrated	YES
HW Calibration	NO
Auto Brightness	NO
Flicker safe	YES
Reader Mode	YES
Colour Weakness	YES
Super Resolution+	YES
1ms Motion Blur Reduction	NO
NVIDIA G-Sync™	NO
RADEON FreeSync™	YES
FreeSync	NO
Black Stabilizer	YES
Dynamic Action Sync	YES
Crosshair	NO
Sphere Lighting	NO
PBP	NO
PIP	NO
Smart Energy Saving	YES

COLOUR

Front	Black
B/Cover	White
Stand	Silver
Base	Silver
Others	Silver



MECHANICAL

Display Position Adjustments	Tilt / Height / Pivot
Wall Mountable	100 x 100 mm

SIZE (MM)

Set (with Stand)	613.1 x 567.3 x 230 (Up)
Set (without Stand)	613.1 x 364.4 x 44.6
Box	694 x 213 x 502
Wall Mount size (mm)	100 x 100

WEIGHT (KG)

Set (with Stand)	6.2
Set (without Stand)	4.6
Box	9.0

ACCESSORY

D-Sub	NO
DVI-D	NO
HDMI	YES
Display Port	YES
mDP to DP	NO
Thunderbolt	NO
USB Type C	NO
USB Type C to A Gender	NO
USB A to B	NO
USB3.0 Upstream Cable	NO
PC Audio	NO
Remote Controller	NO