



**40W**

VT-8-41 40W LED BATTEN FITTING-121CM WITH SAMSUNG CHIP  
COLROCODE:4000K -5 YRS WARRANTY

|                       |                          |                                    |
|-----------------------|--------------------------|------------------------------------|
| Lumens<br><b>4800</b> | Beam Angle<br><b>120</b> | Dimensions<br><b>1220x180x69mm</b> |
|-----------------------|--------------------------|------------------------------------|

Day White  
SKU:753

**5 YEARS**  
WARRANTY



## Technical Information

|                |                  |                        |                  |
|----------------|------------------|------------------------|------------------|
| Watts:         | 40               | Dimmable:              | No               |
| Lumens:        | 4800             | Warranty (Years):      | 5                |
| Beam Angle:    | 120              | PF:                    | >0.9             |
| Body Type:     | PC+Iron          | CRI:                   | >80              |
| Long life:     | 30,000 Hours     | Operation Temperature: | -20°C to +45°C   |
| LED Chip Type: | SMD-Samsung Chip | Input Power:           | AC:220-240V/50Hz |
| IP Rating:     | IP20             | Sensor Compatibility:  | Yes              |

## Features

- ✓ Nano plastic tube has better light transmittance
- ✓ Higher Endurance and Longevity than PC and Glass
- ✓ Cost effective, safe retrofit for T8 Tubes
- ✓ Highly Efficient LED Samsung Chip
- ✓ This new material has super thermal conductivity
- ✓ Constant current Integrated IC driver
- ✓ The thickness of a Nano plastic tube is just 0.4 to 0.5 mm
- ✓ Light emitted is even across the angle and hence diffuses the glare
- ✓ Instant start less than 0.5 Seconds
- ✓ Available in 60 cm, 120 cm, 150 cm & 180 cm
- ✓ Complies with LM80
- ✓ Applications - Domestic and Commercial Lighting, Offices, Supermarkets, Shops, Hotels and many more



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Listing Details

EAN Code 3800157638166

Commodity Code 9405403990

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES