



48W

VT-1549 48W LED WATERPROOF LAMP FITTING COLORCODE:6500K

Lumens 4000	Beam Angle 120	Dimensions 1500x60x35mm
-----------------------	--------------------------	-----------------------------------

White
SKU:6468

2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Watts:	48	IP Rating:	IP65
Lumens:	4000	Dimmable:	No
On/Off Cycles::	>15000	Warranty (Years):	2
Beam Angle:	120	PF:	>0.9
Unit Color:	White	CRI:	>80
Body Type:	Plastic	Operation Temperature:	-20°C to +45°C
Long life:	20,000 Hours	Input Power:	AC:200-240V,50/60Hz
LED Chip Type:	SMD2835	Sensor Compatibility:	Yes

Features

- ✓ Using high power SMD technology which makes it more reliable and durable
- ✓ Complete protection from water, dust and corrosion - IP65 Rated
- ✓ Easy Installation by direct wiring
- ✓ Designed for maximum efficiency & minimal glare
- ✓ Efficient LED arrays with integrated aluminium heatsink for excellent heat dissipation
- ✓ Save up to 80% in electricity consumption compared to a fluorescent lighting fixture
- ✓ Long Lifespan, Low maintenance and energy saving
- ✓ Applications - Parking Lots, Warehouses, Garages, Storage Docks, Workshops and many more



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.485776
Unit CBM	0.005406

Listing Details

EAN Code	3800157640985
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	16
---------------------------------	----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES