



48W

VT-1574 LED WP G-SERIES ECONOMICAL TUBE 150CM
 COLORCODE:6400K

Lumens 3840	Beam Angle 120	Dimensions 1500x65x58mm
-----------------------	--------------------------	-----------------------------------

White
 SKU:6286



Technical Information

Instant Start: 0-100% in 1s	IP Rating: IP65
Watts: 48	Dimmable: No
Lumens: 3840	Warranty (Years): 2
On/Off Cycles: >10000	PF: >0.9
Beam Angle: 120	CR: >70
Unit Color: White	Operation Temperature: -25 to +50°C
Body Type: Plastic	Input Power: AC:200-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes
LED Chip Type: SMD	



Features

- ✓ Waterproof fittings inclusive of T8 LED Tubes
- ✓ Transparent PC diffuser with higher light transmittance
- ✓ Opaque ABS housing with good mechanical performance
- ✓ PG11 waterproof cable gland available for wiring input on one side of the housing
- ✓ Silicon gel gasket and PC clips ensuring IP65 protection
- ✓ Available in 120 cm and 150 cm
- ✓ Long Lifespan, Low maintenance and energy saving
- ✓ Applications - Parking Lots, Warehouses, Garages, Storage Docks, Workshops and many more

Packaging

Unit Details

Gross Weight(GW) Kgs	1.2
Length(Box)mm	1570
Width(Box)mm	70
Height(Box)mm	60
Unit CBM	0.006594

Listing Details

EAN Code	3800157616508
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	144

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES