



Einhell

EXPERT PLUS



Cordless Rotary Hammer

HEROCCO

Item No.: 4513900

Ident No.: 11017

Bar Code: 4006825630343

The Einhell cordless rotary hammer Herocco delivers more power and provides longer operation thanks to the brushless motor. Drilling, hammer drilling or chiseling with or without lock make it a valued allrounder. It is a member of the Power X-Change family. The pneumatic impact mechanism makes effortless progress through concrete. Tools can be changed quickly thanks to the universal SDS-plus tool chuck with auto-slip-in function. The ergonomic grip area provides a firm soft grip hold. The LED light illuminates the work area. Supplied with a magnetic bit adapter for screwing in a transport and storage case E-Box. The batteries and charger are available separately. For optimum operation it is recommended to use a 3.0 Ah battery or higher.

Features & Benefits

- A member of the Power X-Change family
- Brushless motor - more power and prolonged operation
- 4 functions: Drilling/impact drilling/chiseling with and w/o lock
- Pneumatic impact mechanism for effortless drilling in concrete
- Universal SDS-plus chuck with semi-automatic function
- Speed electronics for fine adjustment on delicate jobs
- Low-vibration operations by vibration-cushioned main handle
- Ergonomic handle and additional handle with soft grip
- Infinitely adjustable drilling depth stop made of solid metal
- Incl. LED lamp to illuminate the work area
- Incl. magnetic bit adapter for screwing
- Recommendation for optimum results: 3.0 Ah battery & higher
- Supplied without battery and charger (available separately)
- Supplied in transport and storage case E-Box





Technical Data

- | | |
|---------------------------------|--------------------------|
| - Idle speed (gear 1) | 0-1200 min ⁻¹ |
| - Impact rate (gear 1) | 0-5500 min ⁻¹ |
| - Impact power | 2.2 J |
| - Drilling capacity in concrete | 20 mm |

Logistic Data

- | | |
|--------------------------------------|--------------------|
| - Pieces per export carton | 4 Pieces |
| - Gross weight export carton | 18.5 kg |
| - Tool weight | 2.12 kg |
| - Gross Weight | 4.38 kg |
| - Dimensions single packaging | 400 x 360 x 120 mm |
| - Dimensions export carton | 505 x 415 x 370 mm |
| - Container quantity (20"/40"/40"HC) | 1248 2592 3024 |



Available as special accessories



18V 2,0 Ah Power-X-Change
Battery
Item No.: 4511395
Bar Code: 4006825610369
Einhell Accessory



18V 4,0 Ah Power-X-Change
Battery
Item No.: 4511396
Bar Code: 4006825610376
Einhell Accessory



18V 2,6Ah P-X-C Plus
Battery
Item No.: 4511436
Bar Code: 4006825616590
Einhell Accessory



18V 30min Power-X-Change
Charger
Item No.: 4512011
Bar Code: 4006825587029
Einhell Accessory



18V 5,2 Ah P-X-C Plus
Battery
Item No.: 4511437
Bar Code: 4006825616606
Einhell Accessory



18V 1,5Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512021
Bar Code: 4006825601350
Einhell Accessory



18V 2,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512040
Bar Code: 4006825613681
Einhell Accessory



18V 3,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512041
Bar Code: 4006825613698
Einhell Accessory



18V 4,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512042
Bar Code: 4006825613704
Einhell Accessory



Power-X-Boostcharger 6 A
Charger
Item No.: 4512064
Bar Code: 4006825629019
Einhell Accessory



Power-X-Twincharger 3 A
Charger
Item No.: 4512069
Bar Code: 4006825629729
Einhell Accessory



SDS Drill/chisel set AC 12 pcs
Rotary Hammer Accessory
Item No.: 4258090
Bar Code: 4006825538885
Einhell Grey