



Einhell

EXPERT PLUS



Cordless Impact Driver
TE-CI 18/1 Li (1x2,0Ah)

Item No.: 4510036

Ident No.: 11016

Bar Code: 4006825625103

The Einhell TE-CI 18/1 Li cordless impact driver (1x2.0Ah) masters challenging and delicate jobs. It makes light work of tightening long & large screws. The finely adjustable el. speed control enables delicate work to be performed as well. The low reverse torque reduces strain on the wrists. Short & lightweight in design terms, it has ergonomic Softgrip surfaces. For the standard hexagon mount we recommend impact-resistant bits. Three power LEDs provide good allround illumination. An alu housing and rubber supports make the impact driver a robust tool. The scope of delivery includes one 18 V / 2.0 Ah rechargeable battery and a high-speed charger from the Power X-Change system series, a practical belt clip and a transport and storage case.

Features & Benefits

- A member of the Power X-Change family
- Hammer screwdriver – for effortlessly tightening large/long screw
- Low reverse torque reduces strain on the wrists during operation
- Short, lightweight design with ergonomic Softgrip surfaces
- 1/4 " hex bit mount (Recommendation: impact-resistant bits)
- Speed control for fine adjustment on delicate jobs
- 3 power LEDs included for good allround illumination
- Rugged aluminium housing and rubber supports for protection
- Practical belt clip for efficient and safe operation
- Supplied with 2,0 Ah battery and fast charger
- Supplied with practical case





Technical Data

- | | |
|-----------------------------------|----------------------------|
| - Accumulator | 18 V 2000 mAh Li-Ion |
| - Charging time | 40min |
| - Mains supply of battery charger | 200-250 V 50-60 Hz |
| - Idle speed | 0 - 2300 min ⁻¹ |
| - Type of bit interlock | Mechanic locking sleeve |
| - tool collet (hex) | Bit holder (6,35mm/¼") |
| - Max. torque hard | 140 Nm |
| - Number of accumulators | 1 Pieces |

Logistic Data

- | | |
|--------------------------------------|--------------------|
| - Product weight (kg) | 1.55 |
| - Gross weight (kg) | 3.7 |
| - Pieces per export carton | 4 Pieces |
| - Gross weight export carton | 16 kg |
| - Dimensions Export Carton | 455 x 365 x 345 mm |
| - Container quantity (20"/40"/40"HC) | 1952 4048 0 |



Available as special accessories



18V 2,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512040
Bar Code: 4006825613681
Einhell Accessory



18V 4,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512042
Bar Code: 4006825613704
Einhell Accessory



18V 2,6Ah P-X-C Plus
Battery
Item No.: 4511436
Bar Code: 4006825616590
Einhell Accessory



18V 30min Power X-Change
Charger
Item No.: 4512011
Bar Code: 4006825587029
Einhell Accessory



18V 5,2 Ah P-X-C Plus
Battery
Item No.: 4511437
Bar Code: 4006825616606
Einhell Accessory



Power-X-Boostcharger 6 A
Charger
Item No.: 4512064
Bar Code: 4006825629019
Einhell Accessory



Power-X-Twincharger 3 A
Charger
Item No.: 4512069
Bar Code: 4006825629729
Einhell Accessory



18V 2,0 Ah Power-X-Change
Battery
Item No.: 4511395
Bar Code: 4006825610369
Einhell Accessory



18V 4,0 Ah Power-X-Change
Battery
Item No.: 4511396
Bar Code: 4006825610376
Einhell Accessory



18V 1,5Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512021
Bar Code: 4006825601350
Einhell Accessory



18V 3,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512041
Bar Code: 4006825613698
Einhell Accessory