



Einhell

EXPERT Plus

POWER X CHANGE

TE-TK 18 Li Kit (CD+AG)

Power Tool Kit

Item No.: 4257211

Ident No.: 11015

Bar Code: 4006825613711

The Einhell TE-TK 18 Li Kit (CD+AG) is a set which comprises two Power X-Change members: The TE-CD 18/2 Li drill & driver and the TE-AG 18 Li angle grinder, plus one 1.5 Ah and one 3.0 Ah battery and a 30 minute high-speed charger. The TE-CD 18/2 Li drill & driver with powerful motor and two-speed metal gearing has a Quick Stop function, torque slip coupling and a single-sleeve quick-change drill chuck. The TE-AG 18 Li angle grinder is the lightest angle grinder of its class. The Softstart function ensures that it starts up smoothly, the restart safeguard makes it safer to use and the modified air guidance provides better cooling. The wheel guard comes with a quick-adjust facility for adjustment to every situation.

Features

- Power X-Change tool kit
- TE-CD 18/2 Li cordless drill & driver
- Powerful motor and 2-speed metal gearing
- Single-sleeve chuck with quick-stop
- TE-AG 18 Li cordless angle grinder
- Lightest angle grinder in its class
- Softstart function and restart safeguard to make it safer to use
- Modified air guidance for better cooling and longer service life
- Disk guard with quick adjust facility
- Incl. 1.5 Ah & 3.0 Ah battery and high-speed charger
- Torque slip coupling for sensitive operation



Technical Data

- **Battery:** 18 Volt; Li-Ionen; 1.500 mAh and 3.000 mAh
- **Cordless Drill:**
 - Idle speed: 1st gear: 0 – 350 min⁻¹
2nd gear: 0 – 1.250 min⁻¹
 - Torque setting: 20 + 1
 - Torque: 44 Nm
- **Cordless All Purpose Saw:**
 - Size of grinding wheel cover: 115 mm
 - No-load speed (idle speed) Max: 8500 min⁻¹
 - Max. cutting depth: 28 mm



Logistic Data

- Product weight 3.3 kg
- Gross weight single packaging 5.6 kg
- Dimensions single packaging 315 x 235 x 220 mm
- Pieces per export carton 2 Pieces
- Gross weight export carton 11.3 kg
- Dimensions export carton 505 x 340 x 245 mm
- Container quantity (20"/40"/40"HC) 1334 | 2762 | 3240

