



Main

Range of product	Harmony XB5
Bezel material	Plastic
Product or component type	Fuse carrier
Mounting diameter	22 mm

Complementary

Product compatibility	Fuse 5 x 20 mm, 6.3 A - 250 V
Resistance to high pressure washer	7000000 Pa at 55 °C, distance: 0.1 m
Product weight	0.022 kg

Environment

protective treatment	TH
ambient air temperature for storage	-40...70 °C
ambient air temperature for operation	-25...70 °C
electrical shock protection class	Class II
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 13 NEMA 4X
IK degree of protection	IK03 conforming to EN 50102 IK03 conforming to IEC 50102
standards	EN 60947-1 EN 60947-5-1 EN 60947-5-4 JIS C 4520 UL 508 CSA C22.2 No 14
product certifications	BV CSA DNV GL LROS (Lloyds register of shipping) RINA UL listed

Contractual warranty

Warranty period	18 months 18 months
-----------------	---------------------