



### Main

|                                       |                                |
|---------------------------------------|--------------------------------|
| Accessory / separate part designation | Pre-wired M23 female connector |
| Accessory / separate part destination | Incremental encoder            |
| Accessory / separate part category    | Connection accessories         |
| Accessory / separate part type        | Pre-wired connector            |
| Cable length                          | 2 m                            |
| Total number of wires                 | 10                             |
| Shape of connector                    | Straight                       |

### Complementary

|                |         |
|----------------|---------|
| Product weight | 0.16 kg |
|----------------|---------|

### Offer Sustainability

|                        |   |
|------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 0701 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                  | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

## Wiring Diagram

---

### Pre-wired Connector Connections

| Pin number | Function | Colour |
|------------|----------|--------|
| 1          | A/       | BN     |
| 2          | V Supply | RD     |
| 3          | Top 0    | VT     |
| 4          | Top 0/   | BU     |
| 5          | B        | YE     |
| 6          | B/       | OG     |
| 7          | R        | -      |
| 8          | A        | GN     |
| 9          | R        | -      |
| 10         | Gnd      | BK     |
| 11         | Gnd      | WH     |
| 12         | V Supply | GY     |

R: reserved, do not connect