

Han M23 06 Female -E



| | |
|--------------------|---|
| Part number | 09 15 106 2703 |
| Specification | Han M23 06 Female -E |
| HARTING eCatalogue | https://b2b.harting.com/09151062703 |

Identification

| | |
|----------|-----------------------------|
| Category | Inserts |
| Series | Han [®] M23 Signal |
| Element | Inserts |

Version

| | |
|--------------------|--|
| Termination method | PCB solder termination |
| Gender | Female |
| Number of contacts | 6 |
| Details | Suitable for bulkhead mounted housings 09 15 100 0301, 0302, 0305, 0306 and 0307 only! |

Technical characteristics

| | |
|-----------------------|----------------------|
| Rated current | 20 A |
| Rated voltage | 300 V |
| Rated impulse voltage | 2.5 kV |
| Pollution degree | 3 |
| Insulation resistance | > 10 ¹⁰ Ω |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | ≥500 |

Material properties

| | |
|---------------------|--------------|
| Material (insert) | Polyamide |
| Colour (insert) | White |
| Material (contacts) | Copper alloy |



Pushing Performance

Material properties

| | |
|---|--|
| Surface (contacts) | Gold plated |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant with exemption |
| RoHS exemptions | 6c: Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Specifications and approvals

| | |
|----------|-----------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
|----------|-----------------------|

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 5 |
| Net weight | 7.8 g |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| eCl@ss | 27440205 Contact insert for industrial connectors |