




## ES351TX.CR.BG

High precision Ergo-tek Slim Tungsten carbide Cutters - Large Tapered head, Tungsten carbide tips, flush. OAL: 118 mm. ESD safe



- Engineered for hard wires
- Tungsten carbide blades
- 81 HRC hardness

**Tungsten Carbide sharp tip - Large Tapered diagonal cutters**

*Tungsten carbide cutter leaflet*

## Documents

Grip handle material TDS

## Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	Tungsten Carbide Cutters
Kit	no
ESD safe	yes

<b>Body material</b>	100Cr6
<b>Tip material</b>	TX
<b>Grip handle material</b>	Ergo-tek Slim - TPE + PP
<b>Head shape</b>	Tapered
<b>Head width (mm - in) - C</b>	12.50 - 0.492
<b>Size/type</b>	Large
<b>Cutting edges</b>	Flush
<b>OAL (mm - in) - A</b>	118.00 - 4.646
<b>B (mm - in)</b>	7.50 - 0.295
<b>Head thickness (mm - in) - D</b>	6.40 - 0.252
<b>E (mm - in)</b>	0.70 - 0.028
<b>F (mm - in)</b>	0.40 - 0.016
<b>Net weight (g-lb)</b>	83 - 0.183
<b>RoHS compliant</b>	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland  
T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com