



ES5131.CR.BG

High precision Ergo-tek Slim Cutters - Micro Oval head, flush. OAL: 120 mm. ESD safe



Very slim, oval to maximize accessibility

High precision Cutters & Pliers leaflet

Documents

 Grip handle material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	High Precision Cutters
Kit	no
ESD safe	yes
Body material	100Cr6
Grip handle material	Ergo-tek Slim - TPE + PP
Head shape	Oval

Head width (mm - in) - C	8.00 - 0.315
Size/type	Micro
Cutting edges	Flush
OAL (mm - in) - A	120.00 - 4.724
B (mm - in)	7.00 - 0.276
Head thickness (mm - in) - D	5.00 - 0.197
F (mm - in)	0.50 - 0.02
Cutting capacity soft (mm)	0.8
Cutting capacity soft (AWG)	20
Cutting capacity medium (mm)	0.2
Cutting capacity medium (AWG)	32
Net weight (g-lb)	70 - 0.154
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland
T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com