




277CFR.SA.1

Plastic replaceable tip tweezers - Carbon fiber - tips: curved, fine. OAL: 120mm. ESD saf



Fine, curved tips

OAL 5" 130 mm

B 0.020" 0.5 mm

A 0.028" 0.7 mm

Documents

Tip material TDS

Body material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes

Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	Plastic Replaceable Tip Tweezers
Kit	no
Tip style	277
Tip type characteristic	fine
Bent / angled / curved tip	curved
Reverse action	no
Handle serration(y/n)	no
Locking system	no
ESD safe	yes
Body material	SA
Tip material	CF
Product OAL (mm - in)	120.00 - 4.724
Product width (mm - in)	20.00 - 0.787
Product height (mm - in)	16.00 - 0.63
Tip length (mm - in)	30.00 - 1.181
Tip thickness A (mm - in)	0.70 - 0.028
Tip width B (mm - in)	0.50 - 0.02
Tip opening gap (mm - in)	8 - 0.315
Degree of bending	55
Net weight (g-lb)	18 - 0.04
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com

