




# 710.SV

Full plastic tweezers - PVDF - tips: angled, squared, flat, trapezoidal shape. OAL: 115mm  
ESD safe



Fine padle tips

OAL 4 1/2" 115 mm

A 0.012" 0.3 mm

B 0.30" 7.7 mm



C 4.45" 11.3 mm

## Documents



Body material TDS

## Product included in the following kit/kits

Article code	Family	Category	Full description
<b>K5PISV</b> 	Tweezers	Full Plastic Tweezers	Kit of 5 PVDF tweezers : 702A, 707, 708, 709, 710. ESD safe
<b>K6PISV</b> 	Tweezers	Full Plastic Tweezers	Kit of 6 PVDF tweezers : 702A, 705, 707, 708, 709, 710. ESD safe



## Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Category	Full Plastic Tweezers
Kit	no
Tip style	710
Tip type characteristic	squared
Bent / angled / curved tip (y/n)	no
Reverse action	no
Handle serration(y/n)	no
Tip serration (y/n)	no
Locking system	no
ESD safe	yes
Body material	SV
Product OAL (mm - in)	115.00 - 4.528
Product width (mm - in)	12.00 - 0.472
Product height (mm - in)	11.00 - 0.433
Tip thickness A (mm - in)	0.30 - 0.012
Tip width B (mm - in)	7.70 - 0.303
Tip opening gap (mm - in)	4.00 - 0.157
Net weight (g-lb)	6 - 0.013
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

