




## A272CF

Kit of 2 Carbon fiber tips and 3 screws - tips: tips: straight, flat, squared. OAL: 40mm. ESD safe



Flat squared tips

OAL 1.575" 40 mm

B 0.118" 3.0 mm

A 0.028" 0.7 mm

## Documents

 Tip material TDS

## Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	Plastic Tweezer Tips
Kit	no
Tip style	272
Tip type characteristic	flat, squared

<b>Bent / angled / curved tip (y/n)</b>	no
<b>Reverse action</b>	no
<b>Handle serration(y/n)</b>	no
<b>Locking system</b>	no
<b>ESD safe</b>	yes
<b>Tip material</b>	CF
<b>Product OAL (mm - in)</b>	40.00 - 1.575
<b>Product width (mm - in)</b>	8.00 - 0.315
<b>Product height (mm - in)</b>	3.50 - 0.138
<b>Tip thickness A (mm - in)</b>	0.70 - 0.028
<b>Tip width B (mm - in)</b>	3.00 - 0.118
<b>Tip opening gap (mm - in)</b>	0 -
<b>Net weight (g-lb)</b>	1.5 - 0.003
<b>RoHS compliant</b>	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com