

TECHNICAL DATA SHEET

PRO-POWER

FLEXIBLE, HALOGEN FREE, POLYOLEFIN HEAT SHRINK TUBING

RoHS
Compliant

Model: SHW-1-H (2X)

Applications

- Halogen Free
- Operating temperature -55°C to +125°C
- Minimum shrink temperature 70°C
- Full recovery temperature: 125°C
- Shrink Ratio 2:1
- RoHS Compliant Meets Sony-SS-00259
- Standard Colors: Black, red, blue, yellow, green, white (Other colors are also available on request)



Applications

SHW-1-H series of heat shrink tubing is manufactured with modified radiation cross-linked polyolefin. The specially designed halogen free formulation makes the tubing very flexible and shrinks at lower temperature. Suitable for applications where temperature sensitive components protection, e.g. PVC jacketed wire and cable and quick shrinkage is required. It has good mechanical and electrical performances.

Technical Data

Property	Test Method	Typical Data
Tensile Strength	ASTM D2671	≥10.4 Mpa
Ultimate Elongation	ASTM D2671	≥200%
Longitudinal Shrinkage	UL 224	+/-5%
Heat Aging Tensile Strength Ultimate Elongation	158°C, 168hr	≥7.3 Mpa ≥100%
Heat shock	250°C, 4hrs	No cracking, No dripping
Flammability	FMVSS302	Pass
Dielectric Strength	ASTM D150	≥15 kV/mm
Volume Resistivity	ASTM D2671	≥1x10 ¹⁴ Ω·cm
Copper Stability	UL224	Pass
Copper Corrosion	UL224	No corrosion

Product Dimensions (inch/mm)

Size		As supplied		After Recovery(mm)		Standard Package
Inch	mm	Internal diameter (mm)	Wall thickness (mm)	Internal diameter Max(mm)	Wall thickness (mm)	Spool Length (m/spool)
3/64	1.2	1.1±0.2	0.18±0.05	0.50	0.33+/-0.10	200
1/16	1.6	1.5±0.2	0.20±0.05	0.65	0.36+/-0.10	200
3/32	2.4	2.5±0.2	0.20±0.05	1.00	0.45+/-0.10	200
1/8	3.2	3.5±0.2	0.20±0.05	1.50	0.45+/-0.10	200
3/16	4.8	5.0±0.2	0.28±0.05	2.30	0.56+/-0.10	100
1/4	6.4	6.5±0.2	0.28±0.05	3.0	0.56+/-0.10	100
5/16	7.9	8.5±0.3	0.30±0.08	4.0	0.56+/-0.10	100
3/8	9.5	9.5±0.3	0.30±0.08	4.5	0.56+/-0.10	100
1/2	12.7	12.5±0.3	0.30±0.08	6.0	0.56+/-0.10	100
5/8	15.9	16.5±0.4	0.35±0.10	8.0	0.70+/-0.10	100
3/4	19.0	19.0±0.5	0.35±0.10	9.0	0.70+/-0.10	100
1	25.4	26.0±0.5	0.45±0.12	12.5	0.90+/-0.15	50
1-1/4	31.7	31.5±1.0	0.45±0.12	15.0	1.00+/-0.15	50
1-1/2	38.1	41.5±1.0	0.50±0.12	20.0	1.00+/-0.15	50
2	50.8	≥50	0.50±0.15	25.0	1.10+/-0.20	25
3	76.2	≥80	0.65±0.20	40.0	1.46+/-0.20	25
4	101.6	≥100	0.65±0.20	50.0	1.46+/-0.20	25
5	127	≥120	0.65±0.20	60.0	1.46+/-0.20	25
6	152.4	≥150	0.65±0.20	75.0	1.46+/-0.20	25
7	177.8	≥180	0.65±0.20	90.0	1.46+/-0.20	25

Product Code Table

Description.	Product Code
Heatshrink Tubing Normal Wall 2:1 Black 1.60mm 100m	13633
Heatshrink Tubing Normal Wall 2:1 Black 2.40mm 100m	13634
Heatshrink Tubing Normal Wall 2:1 Black 3.20mm 100m	13635
Heatshrink Tubing Normal Wall 2:1 Black 4.80mm 100m	13636
Heatshrink Tubing Normal Wall 2:1 Black 6.40mm 100m	13637
Heatshrink Tubing Normal Wall 2:1 Black 9.50mm 100m	13638
Heatshrink Tubing Normal Wall 2:1 Black 12.70mm 100m	13639
Heatshrink Tubing Normal Wall 2:1 Black 19.00mm 100m	13640
Heatshrink Tubing Normal Wall 2:1 Black 25.40mm 50m	13641
Heatshrink Tubing Normal Wall 2:1 Black 38.10mm 50m	13642
Heatshrink Tubing Normal Wall 2:1 Black 50.80mm 25m	13643
Heatshrink Tubing Normal Wall 2:1 Black 1.60mm 5m	13644

Heatshrink Tubing Normal Wall 2:1 Black 2.40mm 5m	13645
Heatshrink Tubing Normal Wall 2:1 Black 3.20mm 5m	13646
Heatshrink Tubing Normal Wall 2:1 Black 4.80mm 5m	13647
Heatshrink Tubing Normal Wall 2:1 Black 6.40mm 5m	13648
Heatshrink Tubing Normal Wall 2:1 Black 9.50mm 5m	13649
Heatshrink Tubing Normal Wall 2:1 Black 12.70mm 5m	13650
Heatshrink Tubing Normal Wall 2:1 Black 19.00mm 5m	13651
Heatshrink Tubing Normal Wall 2:1 Black 25.40mm 5m	13652
Heatshrink Tubing Normal Wall 2:1 Black 38.10mm 5m	13653
Heatshrink Tubing Normal Wall 2:1 Black 50.80mm 5m	13654
Heatshrink Tubing Normal Wall 2:1 Clear 1.60mm 100m	13655
Heatshrink Tubing Normal Wall 2:1 Clear 2.40mm 100m	13656
Heatshrink Tubing Normal Wall 2:1 Clear 3.20mm 100m	13657
Heatshrink Tubing Normal Wall 2:1 Clear 4.80mm 100m	13658
Heatshrink Tubing Normal Wall 2:1 Clear 6.40mm 100m	13659
Heatshrink Tubing Normal Wall 2:1 Clear 9.50mm 100m	13660
Heatshrink Tubing Normal Wall 2:1 Clear 12.70mm 100m	13661
Heatshrink Tubing Normal Wall 2:1 Clear 19.00mm 100m	13662
Heatshrink Tubing Normal Wall 2:1 Clear 25.40mm 50m	13663
Heatshrink Tubing Normal Wall 2:1 Clear 38.10mm 50m	13664
Heatshrink Tubing Normal Wall 2:1 Clear 50.80mm 25m	13665
Heatshrink Tubing Normal Wall 2:1 Clear 1.60mm 5m	15034
Heatshrink Tubing Normal Wall 2:1 Clear 2.40mm 5m	15035
Heatshrink Tubing Normal Wall 2:1 Clear 3.20mm 5m	15036
Heatshrink Tubing Normal Wall 2:1 Clear 4.80mm 5m	15037
Heatshrink Tubing Normal Wall 2:1 Clear 6.40mm 5m	15038
Heatshrink Tubing Normal Wall 2:1 Clear 9.50mm 5m	15039
Heatshrink Tubing Normal Wall 2:1 Clear 12.70mm 5m	15040
Heatshrink Tubing Normal Wall 2:1 Clear 19.00mm 5m	15041
Heatshrink Tubing Normal Wall 2:1 Clear 25.40mm 5m	15042
Heatshrink Tubing Normal Wall 2:1 Clear 38.10mm 5m	15043
Heatshrink Tubing Normal Wall 2:1 Clear 50.80mm 5m	15044
Heatshrink Tubing Normal Wall 2:1 Red 1.60mm 100m	13666
Heatshrink Tubing Normal Wall 2:1 Red 2.40mm 100m	13667
Heatshrink Tubing Normal Wall 2:1 Red 3.20mm 100m	13668
Heatshrink Tubing Normal Wall 2:1 Red 4.80mm 100m	13669
Heatshrink Tubing Normal Wall 2:1 Red 6.40mm 100m	13670
Heatshrink Tubing Normal Wall 2:1 Red 9.50mm 100m	13671
Heatshrink Tubing Normal Wall 2:1 Red 12.70mm 100m	13672
Heatshrink Tubing Normal Wall 2:1 Red 19.00mm 100m	13673
Heatshrink Tubing Normal Wall 2:1 Red 25.40mm 50m	13674
Heatshrink Tubing Normal Wall 2:1 Red 38.10mm 50m	13675
Heatshrink Tubing Normal Wall 2:1 Red 50.80mm 25m	13676

Heatshrink Tubing Normal Wall 2:1 Red 1.60mm 5m	15045
Heatshrink Tubing Normal Wall 2:1 Red 2.40mm 5m	15046
Heatshrink Tubing Normal Wall 2:1 Red 3.20mm 5m	15047
Heatshrink Tubing Normal Wall 2:1 Red 4.80mm 5m	15048
Heatshrink Tubing Normal Wall 2:1 Red 6.40mm 5m	15049
Heatshrink Tubing Normal Wall 2:1 Red 9.50mm 5m	15050
Heatshrink Tubing Normal Wall 2:1 Red 12.70mm 5m	15051
Heatshrink Tubing Normal Wall 2:1 Red 19.00mm 5m	15052
Heatshrink Tubing Normal Wall 2:1 Red 25.40mm 5m	15053
Heatshrink Tubing Normal Wall 2:1 Red 38.10mm 5m	15054
Heatshrink Tubing Normal Wall 2:1 Red 50.80mm 5m	15055
Heatshrink Tubing Normal Wall 2:1 Yellow 1.60mm 100m	13677
Heatshrink Tubing Normal Wall 2:1 Yellow 2.40mm 100m	13678
Heatshrink Tubing Normal Wall 2:1 Yellow 3.20mm 100m	13679
Heatshrink Tubing Normal Wall 2:1 Yellow 4.80mm 100m	13680
Heatshrink Tubing Normal Wall 2:1 Yellow 6.40mm 100m	13681
Heatshrink Tubing Normal Wall 2:1 Yellow 9.50mm 100m	13682
Heatshrink Tubing Normal Wall 2:1 Yellow 12.70mm 100m	13683
Heatshrink Tubing Normal Wall 2:1 Yellow 19.00mm 100m	13684
Heatshrink Tubing Normal Wall 2:1 Yellow 25.40mm 50m	13685
Heatshrink Tubing Normal Wall 2:1 Yellow 38.10mm 50m	13686
Heatshrink Tubing Normal Wall 2:1 Yellow 50.80mm 25m	13687
Heatshrink Tubing Normal Wall 2:1 Yellow 1.60mm 5m	15056
Heatshrink Tubing Normal Wall 2:1 Yellow 2.40mm 5m	15057
Heatshrink Tubing Normal Wall 2:1 Yellow 3.20mm 5m	15058
Heatshrink Tubing Normal Wall 2:1 Yellow 4.80mm 5m	15059
Heatshrink Tubing Normal Wall 2:1 Yellow 6.40mm 5m	15060
Heatshrink Tubing Normal Wall 2:1 Yellow 9.50mm 5m	15061
Heatshrink Tubing Normal Wall 2:1 Yellow 12.70mm 5m	15062
Heatshrink Tubing Normal Wall 2:1 Yellow 19.00mm 5m	15063
Heatshrink Tubing Normal Wall 2:1 Yellow 25.40mm 5m	15064
Heatshrink Tubing Normal Wall 2:1 Yellow 38.10mm 5m	15065
Heatshrink Tubing Normal Wall 2:1 Yellow 50.80mm 5m	15066
Heatshrink Tubing Normal Wall 2:1 White 1.60mm 100m	13688
Heatshrink Tubing Normal Wall 2:1 White 2.40mm 100m	13689
Heatshrink Tubing Normal Wall 2:1 White 3.20mm 100m	13690
Heatshrink Tubing Normal Wall 2:1 White 4.80mm 100m	13691
Heatshrink Tubing Normal Wall 2:1 White 6.40mm 100m	13692
Heatshrink Tubing Normal Wall 2:1 White 9.50mm 100m	13693
Heatshrink Tubing Normal Wall 2:1 White 12.70mm 100m	13694
Heatshrink Tubing Normal Wall 2:1 White 19.00mm 100m	13695
Heatshrink Tubing Normal Wall 2:1 White 25.40mm 50m	13696
Heatshrink Tubing Normal Wall 2:1 White 38.10mm 50m	13697

Heatshrink Tubing Normal Wall 2:1 White 50.80mm 25m	13698
Heatshrink Tubing Normal Wall 2:1 White 1.60mm 5m	15067
Heatshrink Tubing Normal Wall 2:1 White 2.40mm 5m	15068
Heatshrink Tubing Normal Wall 2:1 White 3.20mm 5m	15069
Heatshrink Tubing Normal Wall 2:1 White 4.80mm 5m	15070
Heatshrink Tubing Normal Wall 2:1 White 6.40mm 5m	15071
Heatshrink Tubing Normal Wall 2:1 White 9.50mm 5m	15072
Heatshrink Tubing Normal Wall 2:1 White 12.70mm 5m	15073
Heatshrink Tubing Normal Wall 2:1 White 19.00mm 5m	15074
Heatshrink Tubing Normal Wall 2:1 White 25.40mm 5m	15075
Heatshrink Tubing Normal Wall 2:1 White 38.10mm 5m	15076
Heatshrink Tubing Normal Wall 2:1 White 50.80mm 5m	15077
Heatshrink Tubing Normal Wall 2:1 Blue 1.60mm 100m	13699
Heatshrink Tubing Normal Wall 2:1 Blue 2.40mm 100m	13700
Heatshrink Tubing Normal Wall 2:1 Blue 3.20mm 100m	13701
Heatshrink Tubing Normal Wall 2:1 Blue 4.80mm 100m	13702
Heatshrink Tubing Normal Wall 2:1 Blue 6.40mm 100m	13703
Heatshrink Tubing Normal Wall 2:1 Blue 9.50mm 100m	13704
Heatshrink Tubing Normal Wall 2:1 Blue 12.70mm 100m	13705
Heatshrink Tubing Normal Wall 2:1 Blue 19.00mm 100m	13706
Heatshrink Tubing Normal Wall 2:1 Blue 25.40mm 50m	13707
Heatshrink Tubing Normal Wall 2:1 Blue 38.10mm 50m	13708
Heatshrink Tubing Normal Wall 2:1 Blue 50.80mm 25m	13709
Heatshrink Tubing Normal Wall 2:1 Blue 1.60mm 5m	15078
Heatshrink Tubing Normal Wall 2:1 Blue 2.40mm 5m	15079
Heatshrink Tubing Normal Wall 2:1 Blue 3.20mm 5m	15080
Heatshrink Tubing Normal Wall 2:1 Blue 4.80mm 5m	15081
Heatshrink Tubing Normal Wall 2:1 Blue 6.40mm 5m	15082
Heatshrink Tubing Normal Wall 2:1 Blue 9.50mm 5m	15083
Heatshrink Tubing Normal Wall 2:1 Blue 12.70mm 5m	15084
Heatshrink Tubing Normal Wall 2:1 Blue 19.00mm 5m	15085
Heatshrink Tubing Normal Wall 2:1 Blue 25.40mm 5m	15086
Heatshrink Tubing Normal Wall 2:1 Blue 38.10mm 5m	15087
Heatshrink Tubing Normal Wall 2:1 Blue 50.80mm 5m	15088
Heatshrink Tubing Normal Wall 2:1 Brown 1.60mm 100m	13721
Heatshrink Tubing Normal Wall 2:1 Brown 2.40mm 100m	13722
Heatshrink Tubing Normal Wall 2:1 Brown 3.20mm 100m	13723
Heatshrink Tubing Normal Wall 2:1 Brown 4.80mm 100m	13724
Heatshrink Tubing Normal Wall 2:1 Brown 6.40mm 100m	13725
Heatshrink Tubing Normal Wall 2:1 Brown 9.50mm 100m	13726
Heatshrink Tubing Normal Wall 2:1 Brown 12.70mm 100m	13727
Heatshrink Tubing Normal Wall 2:1 Brown 19.00mm 100m	13728
Heatshrink Tubing Normal Wall 2:1 Brown 25.40mm 50m	13729

Heatshrink Tubing Normal Wall 2:1 Brown 38.10mm 50m	13730
Heatshrink Tubing Normal Wall 2:1 Brown 50.80mm 25m	13731
Heatshrink Tubing Normal Wall 2:1 Brown 1.60mm 5m	15100
Heatshrink Tubing Normal Wall 2:1 Brown 2.40mm 5m	15101
Heatshrink Tubing Normal Wall 2:1 Brown 3.20mm 5m	15102
Heatshrink Tubing Normal Wall 2:1 Brown 4.80mm 5m	15103
Heatshrink Tubing Normal Wall 2:1 Brown 6.40mm 5m	15104
Heatshrink Tubing Normal Wall 2:1 Brown 9.50mm 5m	15105
Heatshrink Tubing Normal Wall 2:1 Brown 12.70mm 5m	15106
Heatshrink Tubing Normal Wall 2:1 Brown 19.00mm 5m	15107
Heatshrink Tubing Normal Wall 2:1 Brown 25.40mm 5m	15108
Heatshrink Tubing Normal Wall 2:1 Brown 38.10mm 5m	15109
Heatshrink Tubing Normal Wall 2:1 Brown 50.80mm 5m	15110
Heatshrink Tubing Normal Wall 2:1 Grey 1.60mm 100m	13633GRY
Heatshrink Tubing Normal Wall 2:1 Grey 2.40mm 100m	13634GRY
Heatshrink Tubing Normal Wall 2:1 Grey 3.20mm 100m	13635GRY
Heatshrink Tubing Normal Wall 2:1 Grey 4.80mm 100m	13636GRY
Heatshrink Tubing Normal Wall 2:1 Grey 6.40mm 100m	13637GRY
Heatshrink Tubing Normal Wall 2:1 Grey 9.50mm 100m	13638GRY
Heatshrink Tubing Normal Wall 2:1 Grey 12.70mm 100m	13639GRY
Heatshrink Tubing Normal Wall 2:1 Grey 19.00mm 100m	13640GRY
Heatshrink Tubing Normal Wall 2:1 Grey 25.40mm 50m	13641GRY
Heatshrink Tubing Normal Wall 2:1 Grey 38.1mm 50m	13642GRY
Heatshrink Tubing Normal Wall 2:1 Grey 50.8mm 25m	13643GRY
Heatshrink Tubing Normal Wall 2:1 Grey 1.60mm 5m	13644GRY
Heatshrink Tubing Normal Wall 2:1 Grey 2.40mm 5m	13645GRY
Heatshrink Tubing Normal Wall 2:1 Grey 3.20mm 5m	13646GRY
Heatshrink Tubing Normal Wall 2:1 Grey 4.80mm 5m	13647GRY
Heatshrink Tubing Normal Wall 2:1 Grey 6.40mm 5m	13648GRY
Heatshrink Tubing Normal Wall 2:1 Grey 9.50mm 5m	13649GRY
Heatshrink Tubing Normal Wall 2:1 Grey 12.70mm 5m	13650GRY
Heatshrink Tubing Normal Wall 2:1 Grey 19.00mm 5m	13651GRY
Heatshrink Tubing Normal Wall 2:1 Grey 25.40mm 5m	13652GRY
Heatshrink Tubing Normal Wall 2:1 Grey 38.10mm 5m	13653GRY
Heatshrink Tubing Normal Wall 2:1 Grey 50.80mm 5m	13654GRY
Heatshrink Tubing Normal Wall 2:1 Blk Ret Pkd 1.6 5m	HSRP1.6BLK
Heatshrink Tubing Normal Wall 2:1 Blk Ret Pkd 2.4 5m	HSRP2.4BLK
Heatshrink Tubing Normal Wall 2:1 Blk Ret Pkd 3.2 5m	HSRP3.2BLK
Heatshrink Tubing Normal Wall 2:1 Blk Ret Pkd 4.8 5m	HSRP4.8BLK
Heatshrink Tubing Normal Wall 2:1 Blk Ret Pkd 6.4 5m	HSRP6.4BLK
Heatshrink Tubing Normal Wall 2:1 Blk Ret Pkd 9.5 5m	HSRP9.5BLK
Heatshrink Tubing Normal Wall 2:1 Blk Ret Pkd 12.7 5m	HSRP12.7BLK
Heatshrink Tubing Normal Wall 2:1 Nat Ret Pkd 1.6 5m	HSRP1.6NAT

Heatshrink Tubing Normal Wall 2:1 Nat Ret Pkd 2.4 5m	HSRP2.4NAT
Heatshrink Tubing Normal Wall 2:1 Nat Ret Pkd 3.2 5m	HSRP3.2NAT
Heatshrink Tubing Normal Wall 2:1 Nat Ret Pkd 4.8 5m	HSRP4.8NAT
Heatshrink Tubing Normal Wall 2:1 Nat Ret Pkd 6.4 5m	HSRP6.4NAT
Heatshrink Tubing Normal Wall 2:1 Nat Ret Pkd 9.5 5m	HSRP9.5NAT
Heatshrink Tubing Normal Wall 2:1 Nat Ret Pkd 12.7 5m	HSRP12.7NAT
Heatshrink Tubing Normal Wall 2:1 Green 1.60mm 100m	13732
Heatshrink Tubing Normal Wall 2:1 Green 2.40mm 100m	13733
Heatshrink Tubing Normal Wall 2:1 Green 3.20mm 100m	13734
Heatshrink Tubing Normal Wall 2:1 Green 4.80mm 100m	13735
Heatshrink Tubing Normal Wall 2:1 Green 6.40mm 100m	13736
Heatshrink Tubing Normal Wall 2:1 Green 9.50mm 100m	13737
Heatshrink Tubing Normal Wall 2:1 Green 12.70mm 100m	13738
Heatshrink Tubing Normal Wall 2:1 Green 19.00mm 100m	13739
Heatshrink Tubing Normal Wall 2:1 Green 25.40mm 50m	13740
Heatshrink Tubing Normal Wall 2:1 Green 38.10mm 50m	13741
Heatshrink Tubing Normal Wall 2:1 Green 50.80mm 50m	13742
Heatshrink Tubing Normal Wall 2:1 Green 1.60mm 5m	15111
Heatshrink Tubing Normal Wall 2:1 Green 2.40mm 5m	15112
Heatshrink Tubing Normal Wall 2:1 Green 3.20mm 5m	15113
Heatshrink Tubing Normal Wall 2:1 Green 4.80mm 5m	15114
Heatshrink Tubing Normal Wall 2:1 Green 6.40mm 5m	15115
Heatshrink Tubing Normal Wall 2:1 Green 9.50mm 5m	15116
Heatshrink Tubing Normal Wall 2:1 Green 12.70mm 5m	15117
Heatshrink Tubing Normal Wall 2:1 Green 19.00mm 5m	15118
Heatshrink Tubing Normal Wall 2:1 Green 25.40mm 5m	15119
Heatshrink Tubing Normal Wall 2:1 Green 38.10mm 5m	15120
Heatshrink Tubing Normal Wall 2:1 Green 50.80mm 5m	15121
Heatshrink Tubing Normal Wall 2:1 Purple 1.60mm 100m	13793
Heatshrink Tubing Normal Wall 2:1 Purple 2.40mm 100m	13794
Heatshrink Tubing Normal Wall 2:1 Purple 3.20mm 100m	13795
Heatshrink Tubing Normal Wall 2:1 Purple 4.80mm 100m	13796
Heatshrink Tubing Normal Wall 2:1 Purple 6.40mm 100m	13797
Heatshrink Tubing Normal Wall 2:1 Purple 9.50mm 100m	13798
Heatshrink Tubing Normal Wall 2:1 Purple 12.70mm 100m	13799
Heatshrink Tubing Normal Wall 2:1 Purple 19.00mm 100m	13800
Heatshrink Tubing Normal Wall 2:1 Purple 25.40mm 50m	13801
Heatshrink Tubing Normal Wall 2:1 Purple 38.10mm 50m	13802
Heatshrink Tubing Normal Wall 2:1 Purple 50.80mm 25m	13803
Heatshrink Tubing Normal Wall 2:1 Purple 1.60mm 5m	15170
Heatshrink Tubing Normal Wall 2:1 Purple 2.40mm 5m	15171
Heatshrink Tubing Normal Wall 2:1 Purple 3.20mm 5m	15172
Heatshrink Tubing Normal Wall 2:1 Purple 4.80mm 5m	15173

Heatshrink Tubing Normal Wall 2:1 Purple 6.40mm 5m	15174
Heatshrink Tubing Normal Wall 2:1 Purple 9.50mm 5m	15175
Heatshrink Tubing Normal Wall 2:1 Purple 12.70mm 5m	15176
Heatshrink Tubing Normal Wall 2:1 Purple 19.00mm 5m	15177
Heatshrink Tubing Normal Wall 2:1 Purple 25.40mm 5m	15178
Heatshrink Tubing Normal Wall 2:1 Purple 38.10mm 5m	15179
Heatshrink Tubing Normal Wall 2:1 Purple 50.80mm 5m	15180
Heatshrink Tubing Normal Wall 2:1 Bk 1.2mm 100m	13745
Heatshrink Tubing Normal Wall 2:1 Bk 1.2mm 5m	15122
Heatshrink Tubing Normal Wall 2:1 Cl 1.2mm 100m	13749
Heatshrink Tubing Normal Wall 2:1 Cl 1.2mm 5m	15126
Heatshrink Tubing Normal Wall 2:1 Red 1.2mm 100m	13753
Heatshrink Tubing Normal Wall 2:1 Red 1.2mm 5m	15130
Heatshrink Tubing Normal Wall 2:1 Yellow 1.2mm 100m	13757
Heatshrink Tubing Normal Wall 2:1 Yellow 1.2mm 5m	15134
Heatshrink Tubing Normal Wall 2:1 White 1.2mm 100m	13761
Heatshrink Tubing Normal Wall 2:1 White 1.2mm 5m	15138
Heatshrink Tubing Normal Wall 2:1 Blue 1.2mm 100m	13765
Heatshrink Tubing Normal Wall 2:1 Blue 1.2mm 5m	15142
Heatshrink Tubing Normal Wall 2:1 Brown 1.2mm 100m	13773
Heatshrink Tubing Normal Wall 2:1 Brown 1.2mm 5m	15150
Heatshrink Tubing Normal Wall 2:1 Grey 1.2mm 100m	13777
Heatshrink Tubing Normal Wall 2:1 Grey 1.2mm 5m	15154
Heatshrink Tubing Normal Wall 2:1 Orange 1.2mm 100m	13781
Heatshrink Tubing Normal Wall 2:1 Orange 1.2mm 5m	15158
Heatshrink Tubing Normal Wall 2:1 Green 1.2mm 100m	13785
Heatshrink Tubing Normal Wall 2:1 Green 1.2mm 5m	15162
Heatshrink Tubing Normal Wall 2:1 Black 7.90mm 100m	13746
Heatshrink Tubing Normal Wall 2:1 Black 7.90mm 5m	15123
Heatshrink Tubing Normal Wall 2:1 Black 16.00mm 100m	13747
Heatshrink Tubing Normal Wall 2:1 Black 16.00mm 5m	15124
Heatshrink Tubing Normal Wall 2:1 Black 32.00mm 50m	13748
Heatshrink Tubing Normal Wall 2:1 Black 32.00mm 5m	15125

Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.