




# TRIAX

connecting the future



## HTS 2DC - 2 way splitter

Article number: 347012

### Product description:

HTS 2DC - 2 way splitter. Low insertion loss. All ports impedance 75 Ohm. High isolation. Class A shielding - ideal for your TV system.

### Specifications

ORDER INFORMATION	
EAN Number	5702663470125
SHIELDING	
Shielding efficiency VHF/UHF	> 110.0 dB
FREQUENCY	
Frequency range	5...1000 MHz
LOSS	
Insertion loss (in-out) 5-40 Mhz	< 3.3 dB
Insertion loss (in-out) 40-470 MHz	< 3.3 dB
Insertion loss (in-out) 470-860 MHz	< 3.9 dB
Insertion loss (in-out) 860-1000 MHz	< 4.1 dB
ISOLATION	

Isolation (tap-tap) 5-40 MHz	> 28.0 dB
Isolation (tap-tap) 40-470 MHz	> 28.0 dB
Isolation (tap-tap) 470-860 MHz	> 25.0 dB
Isolation (tap-tap) 860-1000 MHz	> 25.0 dB
<b>RETURN LOSS</b>	
Return loss (in-out) 5-40 MHz	> 24.0 / > 24.0 dB
Return loss (in-out) 40-470 MHz	> 22.0 / > 22.0 dB
Return loss (in-out) 470-860 MHz	> 20.0 / > 20.0 dB
Return loss (in-out) 860-1000 MHz	> 20.0 / > 20.0 dB
<b>ELECTRICAL</b>	
Impedance	75 $\Omega$
<b>OPERATIONAL</b>	
DC Passthrough	Yes
<b>CONNECTORS</b>	
Number of outputs	2
Connector Type	F-female
<b>MECHANICAL</b>	
Product Depth	16 mm
Product Height	50 mm
Product Width	52 mm
Packing QTY	1
Packaging Height	0,020 m
Packaging Width	0,050 m
Packaging Depth	0,050 m
Net Weight	0,045 kg
Tara Weight	0,006 kg
Total Weight	0,051 kg