

WXSF 120

Product no.: T0051391199



Benefits

- For solder wire from Ø 0.5 mm - 1.0 mm
- Feed motion, adjustable from 1 - 27.5 mm/s
- Max. solder wire weight 1 kg
- Compatible with Weller WX series and rework base stations (sold separately)
- Pulse mode: the solder wire is continuously delivered as long as the switch is pressed (LED off)
- Integrated start / stop / standby functions conserves energy and extends the service life of the unit



For this purpose, we recommend:



Solder fume extractors



Pre-heating plates



Cleaning




Soldering tips



Technical Data

Active Tip heating element technology	---
Power Response heating element technology	on
Silver Line heating element technology	---
Voltage	24 V AC
Power	120 W (126 W)
Tip range	XT
Supply unit	WX 1, WX 2, WXD 2, WXA 2, WXR 3
WX-compatible	on
Temperature range °C	100 - 450
Temperature range °F	200 - 850
Heating time	14
Safety rest	---
Safety rest (optional)	---
Barrel	T0058763731
Integrated direct extraction	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE