

PU WAD 101

Power unit 105 W
Product no.: T0053268699N



Benefits


For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning




Pre-heating plates



Technical Data

Dimensions L x W x H (mm)	175 x 135 x 102
Dimensions L x W x H (inches)	6,89 x 5,31 x 4,02
Weight (approx.) in kg	2,4 kg
Voltage	230 V
Power	105 W
Channels	1
Temperature range (depends on tool) °C	50 - 450 (550)
Temperature range (depends on tool) °F	---
Temperature accuracy °C	± 9 (± 30)
Temperature accuracy °F	± 17 (± 50)
Temperature stability °C	± 2
Temperature stability °F	± 5
Equipotential bonding socket	Via a 3.5 mm jack bush (initial state-hard-grounded)
Display	LED
Air consumption l/min	10
Operating pressure in bar/psi	4/58
Capacity l/min	max. 10
Vacuum	N.A.

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE