

WR 3000M Set for vertical applications

3-Channel Rework Station, 360 W (400 W) for vertical applications
Product no.: T0053368399N



Benefits

- > Power unit WR 3M, 3 channels with soldering iron WP 80, desoldering iron DXV 80 and hot air iron HAP 200
- > Desoldering iron DXV 80 for vertical applications




For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning




Pre-heating plates



Technical Data

Dimensions L x W x H (mm)	280 x 240 x 103 mm
Dimensions L x W x H (inches)	11,02 x 9,45 x 4,06 Inch
Weight (approx.) in kg	7,3 kg
Voltage	230 V
Power	360 W (400 W)
Channels	3
Temperature range (depends on tool) °C	50 - 550
Temperature range (depends on tool) °F	150 - 950
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding socket	Via 3.5 mm pawl socket on back of device (Hard grounded)
Display	LCD
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	18
Vacuum	0,7 bar

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE