



Main

| | |
|---------------------------------------|--|
| Range of product | ConneXium |
| Product or component type | Ethernet TCP/IP unmanaged switch |
| Concept | Transparent Ready |
| Communication port protocol | Ethernet TCP/IP |
| Port Ethernet | 10BASE-T/100BASE-TX - 8 port(s) copper cable |
| Maximum number of switches in cascade | Unlimited |

Complementary

| | |
|--------------------------------|---|
| Integrated connection type | Shielded RJ45 copper cable |
| Transmission support medium | Twisted shielded pairs cable CAT 5E for copper cable |
| Cable distance between devices | <= 100 m copper cable |
| Ethernet service | Automatic change of polarity Storage and re-routing of received data Auto MDI/MDX Automatic negotiation of 10/100 Mbit/s and duplex mode |
| [Us] rated supply voltage | 24 V |
| Supply voltage limits | 9.6...32 V DC SELV |
| Power consumption in W | 2.6 W |
| Electrical connection | Removable connector 6 ways power supply |
| Mounting support | 35 mm symmetrical DIN rail |
| Marking | CE |
| Local signalling | 1 LED power supply 1 LED per channel copper port activity 1 LED per channel 10 or 100 Mbit/s data rate |
| Ethernet cabling system | TF switches |
| Width | 49.4 mm |
| Height | 144.9 mm |
| Depth | 117.2 mm |
| Product weight | 0.44 kg |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -40...70 °C |
|---------------------------------------|-------------|

| | |
|-------------------------|-------------------------------|
| Relative humidity | 0...95 % without condensation |
| IP degree of protection | IP40 |
| Standards | CSA C22.2 No 142 CUL 508 |
| Product certifications | CE |

Dimensions

