

PYLE

PyleUSA.com









PDWM2234

Wireless BT Streaming UHF Mic System

Adjustable Volume Controls, Includes (2) Handheld Mics

USER MANUAL


- 1. Please read this manual before using this equipment in order to avoid damage through incorrect operation and to get the best performance from your purchase.**
2. Keep the manual for future reference.
3. Please pay due attention to the following symbols to help you use the product safely and properly and to avoid any personal injury or damage to the product.
4. Please read the entire manual strictly and follow these steps to use you product.
5. No user serviceable parts inside transmitter or receiver - refer servicing to qualified service personnel.
6. To prevent the risk of fire or electric shock, do not expose any of the components to rain or moisture.
7. Please keep a good ventilation and dry environment around the entire unit.
8. Keep this system far away from hot object.
9. Ensure that the correct adapter is used with adequate current rating and that the mains voltage is as stated on the adapter.
10. Keep the system away from any ignition source such as the fireplace, heaters or candles.
11. Do not throw used batteries into a fire or garbage bin with domestic rubbish.
Be sure to dispose of used batteries in accordance with local waste disposal rules.
12. Do not place heavy objects or liquid on top of the system
13. Equipment can be used in tropical or temperate zone
14. Do not leave batteries where they are exposed to direct sunlight, or high temperatures. Doing so may result in overheating, explosion or fire.
15. Pull out the power plug for disconnecting the system. Don't use the system under the environment as follow.
Only the certified technician may disassemble the product.





(Amplifier or Mixer)

Human voice and music mixed output



(Receiver)
with bluetooth and Echo



(Handheld Transmitter)

with individual ID code
30 frequencies SYNC

Transmitting Human singing voice


Transmitting music by Bluetooth



(Mobile)


Receiver with Bluetooth Features and Operation


- 1. Power ON/OFF:** Press Power ON, the receiver indicator light (12) is ready.
- 2. Antenna:** Lightly lift up the antenna.
Caution: it can't be turned round.
- 3. Audio Output:** Connect the 6.3mm Audio Output Plug to the MIC input of the amplifier or directly to the mixer, or using the attached extra cable to connect it to a 3.5mm Audio input.
- 4. Bluetooth ON/OFF:** Turn ON the Bluetooth. Press and hold the Bluetooth button for 2 seconds. Bluetooth indicator (13) blinks. Open the Bluetooth of your mobile and search for the receiver Bluetooth Network Name: 'PyleUSA' and enter Bluetooth Password: '0000' to pair. A "bee" sound means the Bluetooth pairing is successful, then you can play music from your mobile.
- 5. Volume:** Adjust the volume
- 6. Echo:** Adjust ECHO if needed
- 7. RF Indicator for A Mic:** When turned on the transmitter, indicator light is lit.
- 8. RF Indicator for B Mic:** When turned on the transmitter, indicator light is lit.
- 9. Battery Indicator: LOW BAT** Indicator light is lit then you will hear a "bee" sound, means you need to recharge it.
- 10. Battery Charging Indicator:** Indicator light is lit while recharging the battery and turns OFF when fully charged.
- 11. USB Port for charging:** 5v, 1000mA



HANDHELD TRANSMITTER FEATURES AND OPERATION

- 1. Power ON/OFF:** Press to power **ON**. Press and hold for 2 seconds to turn **OFF**.
- 2. LCD Display**
- 3. Channel Sync**
- 4. Battery Capacity Indicator:** Indicator light blinks which means you need to recharge it.
- 5. Cartridge Grille:** This protects the microphone cartridge and helps reduce breath sounds and wind noise. Do not cover grille with hand.
- 6. Battery Charging Indicator:** Indicator light is lit while recharging the battery and turns **OFF** when fully charged.
- 7. USB Port for charging:** 5v, 1000mA

 A charging device with the same labeled voltage and current must be used when charging.



Wireless BT Streaming UHF Wireless Microphone System

Adjustable Volume Controls, Includes (2) Handheld Mics

System Features:

- Bluetooth
- VHF Narrow Band Receiver System
- Dual Frequency Design (Channel A/B)
- High Signal/Noise Ratio Performance
- Broad Frequency Response Range & Low Distortion
- Independent Adjustable Volume Control
- Dual Independent Channel Antennas
- RF Signal and AF Signal LED Indicators
- Radio Frequency and Audio Frequency
- Built-in Rechargeable Battery up to 5 Hours Life
- Working Distance Up to 160' Feet

Bluetooth Connectivity:

- Built-in Bluetooth for Wireless Streaming
- Works with All of Your Favorite Devices
(Smartphone, Tablet, Laptop, Computer, etc.)
- Bluetooth Network Name: 'PyleUSA'
- Bluetooth Password: '0000' (U-7298)
- Bluetooth Wireless Range: 65'+ Ft. (10meters)
- Bluetooth Version: 2.0 (4.1)

What's in the Box:

- Receiver Base
- (2) Handheld Microphones

Handheld Microphones:

- RF Power Output: >10dBm
- Modulation Pattern: Digital
- Battery Powered, Transmitters Rechargeable 640mA Lithium Battery

System Receiver:

- Sensitivity: -94dBm (S/N:12dB)
- RF Image Rejection: ≥ 70 dB
- Audio Dynamic Range: 96dB
- T.H.D.: <1%
- S/N Ratio: 70dB
- Neighboring Channel / Interference: 60dBc
- Power: Receiver with 1800mA Rechargeable Lithium Battery
- Receiver Dimensions (L x W x H): 6.89" x 1.96" x 0.86" -inches

PYLE

PyleUSA.com



VISIT US ONLINE:

Have a question?

Need service or repair?

Want to leave a comment?

PyleUSA.com/ContactUs

PYLE