

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2032634385](#)
Status: **Active**
Overview: Coeur CST High-Current Interconnect System
Description: Coeur CST High-Current Male Screw-Mounted Pin, 8.00mm Diameter, 26.15mm Length

Documents:

[Drawing \(PDF\)](#) [Application Specification 2043130001-AS-000 \(PDF\)](#)
[Product Specification 2043130001-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	PCB Headers
Series	203263
Application	Power
CURRENT-MAX-NUMERIC	200.0
Datasheet Order No	987651-8619
Overview	Coeur CST High-Current Interconnect System
Product Name	Coeur CST
UPC	191130137916

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	8.00mm
Durability (mating cycles max)	200
Glow-Wire Capable	No
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	16.361/g
Number of Rows	1
Orientation	Vertical
PCB Thickness - Recommended	2.00mm min.
Packaging Type	Carton
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Screw

Electrical

Current - Maximum per Contact	200.0A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Application Specification	2043130001-AS-000
Product Specification	2043130001-PS-000
Sales Drawing	2032634185-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[203263](#) Series

Mates With

Coeur CST 8.00mm Socket [204365](#) ,
[204318](#) , [204313](#) , [204316](#)