

## TL1550B Test Leads with Alligator Clips (Red, Black, Green)



### Key features

3 Test Leads connected to Low-Leakage Probes (red, black, green), 3 Alligator Clips (red, black, green), Maximum Jaw Opening: 26 mm (1 in.), Replacement Test Lead Set for the Fluke 1550B Meg Ohm Meter Length (Lead Only): 2.6 m (8.6 feet), Cat II 1000 V, Cat II

### Product overview: TL1550B Test Leads with Alligator Clips (Red, Black, Green)

- 3 Test Leads connected to Low-Leakage Probes (red, black, green)
- 3 Alligator Clips (red, black, green)
- Maximum Jaw Opening: 26 mm (1 in.)
- Replacement Test Lead Set for the Fluke 1550B MegOhmMeter
- Length (Lead Only): 2.6 m (8.6 feet)
- Cat II 1000 V, Cat III 600 V, 5kV DC Max (Probes)
- Cat II 1000 V, Cat III 600 V, 20 amps (Alligator Clips)