

MAX003T

- Waterproof and dustproof IP67 certified
- 3-15 adjustable compartments
- Watertight seal around lid
- Automatic pressure release valve
- Stackable interlocking system

Body: polypropylene random

Latches: nylon

O-ring: polymer

COLOUR: transparent

EXTERNAL DIMENSIONS: 350 x 230 x H59mm (13.77 x 9.05 x H2.32 inch)

INTERNAL DIMENSIONS: 316 x 195 x H53mm (12.44 x 7.67 x H2.08 inch)

LID-BOTTOM DEPTH: 16+37mm (0.63+1.46 inch)

WEIGHT: 0.60 kg – 1.32 lbs.

CARTON DIMENSIONS: 370 x 245 x 375mm – 14.57 x 9.65 x 14.76 inch

WEIGHT OF THE FULL CARTON: 3.35 kg – 7.38 lbs.

PCS PER CARTON: 6

MOULDING: injection molded

RANGE TEMPERATURE: -10 / 80°C (14 / 176°F)

CUSTOMIZATION: personalized nameplate/resin label

FEATURES: IP67

