

Han 3EMC-HAE-M25



Part number	19 62 003 1645
Specification	Han 3EMC-HAE-M25
HARTING eCatalogue	https://b2b.harting.com/19620031645

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] EMC
Type of hood/housing	Hoods

Version

Locking type	Single locking lever
Size	3 A
Version	Side entry
Cable entry	1x M25
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

Specifications and approvals

Approvals DNV GL

Commercial data

Packaging size 1

Net weight 80.5 g

Country of origin China

European customs tariff number 8538900000

eCl@ss 27440202 Shell for industrial connectors