

Han Guiding Dummy module, female



Part number	09 14 003 3150
Specification	Han Guiding Dummy module, female
HARTING eCatalogue	https://b2b.harting.com/09140033150

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Guiding module
Description of the module	Dummy module

Version

Gender	Female
--------	--------

Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Lock-in range	±4 mm

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	2
----------------	---



Pushing Performance

Commercial data

Net weight	7.3 g
Country of origin	China
European customs tariff number	8547200000
