

Overhead Closers

Introduction

The Briton 2003 closer is a part of the Briton 2000 Series, which offers adjustable and fixed strength power sizes providing a comprehensive package of solutions to suit most door closing applications

Features & Functions

- Cast aluminium body
- Steel rack and pinion mechanism is heat treated for strength and durability
- Forged, heat treated and ground steel piston for rugged durability.
- High quality hydraulic fluid with built-in temperature compensation ensures reliable performance without the need for seasonal adjustment
- Stylish flatarm arm in finish to match door closer cover.
- The mechanism is safety valve protected to prolong the life of the closer against abuse and misuse.
- Precision needle roller bearings for optimum performance and efficiency
- Classic fabricated cover conceals fixings and adjustment screws, reducing the risk of vandalism. Available in a range of architectural finishes with matching arms or track to complement a variety of doorhardware ranges.
- Briton badge of authenticity.
- Accufit template increases the accuracy of installation and helps to reduce installation time



Certification

CE Marked to EN 1154 (AD0013)


Fire tested to EN 1634 for use on fire doors up to 2hr timber / 4hr steel
Certifire Approved CF111

DoP available at www.britondops.co.uk

Overhead Closer Briton 2003

Product features	2003	Product references
Closer type	Projecting/scissor arm	
Max. door size width - weight	950mm - 60kg	
Fixed closing power EN size	3	
Adjustment type	-	
Maximum angle of opening	180°	
Adjustable closing speed & latch action	■	
Tri-pack armset	■	
Suitable for mounting applications	Parallel arm mount not suitable for a fire door	
Mechanical hold-open facility (non fire doors only)	□	
Cover variants	C (classic)	
Finishes available	SSS,PSS, PBS, SES	
CE Classification	4 8 3-3 1 1 3	

- Standard
- Available as an option/variant



Finishes

All finish variants are supplied with matching armset and brackets

