



121CE

Overhead door controls

Fixed power compact overhead closer suitable for the most popular door sizes. This cost effective closer exhibits the characteristics of performance, durability and quality that specifiers have come to expect from a Briton door closer



Product features	Product references
	121CE
CE marked	■
Fixed closing power EN size	3
Maximum angle of opening	180°
Adjustable closing speed & latch action	■
Regular armset and bracket	■
Parallel armset and bracket	□
Mechanical hold-open armset (non fire doors)	□
Projecting arm closer	■
Guarantee period	10yrs
CE Classification	4 8 3 1 1 3


■ Standard □ Available as an option/variant

Certification

- CE Marked to EN 1154
- Fire tested to EN 1634 for use on timber fire doors up to 2hr
- Certifire Approved
- DoP available at www.britoninspec.co.uk

Features & Functions

- Pressure die cast aluminium body
- Hardened and ground steel rack and pinion mechanism for smooth efficient operation
- Fixed power size EN 3
- Screw thread forged steel armset
- Supplied with fixings for regular door mounting
- Optional parallel arm bracket available
- Adjustable closing speed and latch action
- Available in a choice of sprayed finishes
- Optional hold-open armset. (**Not to be used on fire door applications**)



Allegion (UK) Limited

35 Rocky Lane, Aston, Birmingham B6 5RQ

Tel: +44 (0) 121 380 2400