

ATT-1950 - 19" PA Attenuator



6-way PA volume controls for 482 mm (19") rack installation

- 6 audio transformers for 100 V line technique
- Connection for priority circuit, 6 priority relays (DC current 24 V/20 mA)
- Attenuation in 10 steps, position 0 is OFF
- Aluminium front panel
- Available in 3 power classes
- Plug-in screw terminal

Technical Data

| | |
|-------------------------|---------------------------|
| Frequency range | : 50-18,000 Hz |
| Power rating | : 6 x 50 W _{RMS} |
| Priority facility | : yes |
| Dimensions | : 484x88x77 mm, 2 RS |
| Weight | : 1.6 kg |
| Surface-mounted housing | : - |