



CLIFF

4mm PLUG P14XASR



Nickel plated plug with retractable shroud and cable restraint collet.
Rated 1000V, 10A maximum, CAT II. Max cable Ø4.2mm.
Supplied unassembled.



FCR6381R - Retractable 4mm Plug P14XASR Red
FCR6381B - Retractable 4mm Plug P14XASR Black