

Technical Data

Part Number: X5C5000BM-W

Product Group: CCTV

Product Type: IP Bullet Camera



Xvision 5MP H265+ Bullet IP Camera, 2.7-12mm Motorised Lens, 60m IR, 120dB WDR, Starlight, Video Analytics

Model: X5C5000BM-W	
Style	Bullet Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	No
Mounting Type	Wall or Ceiling
Sensor	1/2.8" Megapixel CMOS Sensor
On Board Camera Functions	Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris, DNR, 120dB WDR, Starlight, Backlight Compensation, Privacy
Resolution	5MP
Lens Type	Motorised
Lens Size	2.7-12mm
Viewing Angle	30-99°

Technical Data

Night Vision	60m IR
Minimum Illumination	0.1 Lux
Video Compression	H265+
Video Streams	Triple Stream
Video Resolution & Frame Rates	2592x1944 - 25fps 2592x1520 - 25fps 2304x1296/2048x1535 - 25fps 1920x1080 - 25fps 1280x720 - 25fps
Video Bitrate	8Kbps - 8Mbps
Network Connection	RJ45 Socket (10/100)
Network Protocols Supported	TCP/IP, HTTP, DHCP, DNS, DDNS, RTP/RTSP, PPPoE, SMTP, NTP, UPnP, SNMP, HTTPS, FTP
Onvif	Yes
Power Over Ethernet (PoE)	Yes
Power Consumption	<9W
Audio Input	Yes
Power Input	12V DC Socket (2.1mm)
On Board Recording	Yes – Micro SD Card Slot (Max 128GB)
Alarm Input	Yes
Video Analytics	Yes - Perimeter Intrusion, Line Crossing, Stationary Object, Pedestrian Detection, Cross Counting, Face Detection
Operating Temperature	-30 ~ 55°
Dimensions (WHD)	Ø84x240mm
Weight (kg)	0.81
Warranty	3 Year Warranty