



**IP20**  
RATED

# ELARA

## 4 LIGHT BAR SPOTLIGHT

**TECHNICAL**

\* Lamps not included

Colour temp	Product code	Wattage	Lamp type
N/A	INL-598410-SNIC	35W Max	4 x GU10*


**GENERAL**

Input voltage	220-240V
Constructional material	Metal & Glass
Class	1
IP rating	IP20
Weight (kg)	1.175kg
Fixings & Instructions supplied	Yes

**PRODUCT DATA**

Product code	Description	Colour	EAN
INL-598410-SNIC	Elara 4 Light Bar Spotlight	Satin Nickel/Chrome	5020024512957

**Dimensions**



**Energy efficiency rating**

This luminaire is compatible with bulbs of the energy classes:

874/2012